

## Power Cord, C14 to C19, H05VV-F, 10A, 2-m (6.56-ft.), Black

MODEL NUMBER: **P047-02M-EU**



Connects a server or PC with a C20 plug to a PDU or UPS with C13 outlets.

### Features

#### Power Cord Connects Equipment in Small Data Centers to Reliable AC Power

This VDE-compliant power cable connects a computer, server, hard drive or other device with a C20 plug to a PDU, UPS system or surge protector with C13 outlets. It can also extend an existing power connection up to two meters (6.6 feet). The P047-02M-EU features an IEC-320-C14 end for connecting to an AC power source and an IEC-320-C19 end for connecting to a device in a small data center or office workstation application that does not require a heavy-gauge connection.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 1.5mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

## Specifications

OVERVIEW	
UPC Code	037332281043
Product Type	Power Extension Cord
Device Compatibility	PDU; Server; UPS
Country/Region	Europe
INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	100-250
PHYSICAL	

### Highlights

- Recommended for powering computers, servers, drives and other network devices
- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

### Package Includes

P047-02M-EU C14 to C19 Power Cable, 2 m (6.6 ft.), Black

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	8.2 mm
Number of Conductors	3
Conductor Gauge	48/0.2AS
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.5
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Shipping Dimensions (hwd / in.)	10.98 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	27.89 x 17.78 x 1.27
Shipping Weight (lbs.)	0.73
Shipping Weight (kg)	0.33
Unit Dimensions (hwd / in.)	10.980 x 7.000 x 0.500
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Relative Humidity	10 ~ 65% RH, Non-Condensing
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C19
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No

STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty