



Powering Business Worldwide

Switch - IEEE 1284 Straight Through Gold Cable - 6-ft.

MODEL NUMBER: P710-006-R

Description

Tripp Lite's 6-ft. IEEE 1284 straight through gold cable connects a computer to a manual or automatic switchbox. It supports high-speed IEEE 1284 bi-directional communication. The cable features gold plated DB25 male/male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

Features

- Connects a computer to a manual or automatic switchbox
- Supports high-speed IEEE 1284 bi-directional communication (modes: standard compatible nibble byte ECP and EPP)
- Length: 6-ft. Connectors: DB25 male/male
- Gold plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- 25 conductor (direct wired)
- Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Features gold-plated connectors for superior conductivity and support of high-speed applications
- Retail packaging

System Requirements

- Computer with a parallel port DB25 Female
- Parallel device or switchbox with a DB25 Female port requiring IEEE communication

Package Includes

- 6-ft. IEEE 1284 AA Straight Thru Parallel Gold Cable DB25M to DB25M

Specifications

OVERVIEW	
UPC Code	037332014443
CONNECTIONS	
Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	DB25 (MALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.50 x 7.25 x 2.25
Shipping Dimensions (hwd / cm)	19.05 x 18.42 x 5.72
Shipping Weight (lbs.)	0.86
Shipping Weight (kg)	0.39



Powering Business Worldwide

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.