

## PDU Power Cord, BS 1363 to C13 - 10A, 250V, H05VV-F, 3 m (9.8 ft.), Black

MODEL NUMBER: P056-03M-UK



Connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet.

### Features

#### Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a PDU or UPS system with a C14 inlet to a BS 1363 wall outlet. It can also connect a computer, server, monitor or other device to a PDU, UPS or surge protector with BS 1363 outlets. Or you can extend an existing power connection up to three meters (9.8 feet). The P056-03M-UK features a BS 1363 end for connecting to an AC power source and an IEC-320-C13 end for connecting to a network device in a data center or other IT application.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

### Highlights

Also recommended for connecting PCs, monitors and servers to AC power. Ideal replacement for a worn-out or missing power cord. VDE-compliant H05VV-F jacket allows use in European IT applications.

### Package Includes

P056-03M-UK C13 to BS 1363 PDU Power Cable, 3 m (9.8 ft.), Black

## Specifications

OVERVIEW	
UPC Code	037332280954
Product Type	Power Extension Cord
Device Compatibility	Computer; PDU; Server
Country/Region	UK
INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	BS1363 UK PLUG



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	IEC-320-C13
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	7.0 mm
Number of Conductors	3
Conductor Gauge	32/0.20AS
Wire Gauge (AWG)	17
Wire Gauge (OD - mm <sup>2</sup> )	1
Power Cord Color	Black
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (cm)	300
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.74
Shipping Weight (kg)	0.34
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.72
Unit Weight (kg)	0.33
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Locking	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.