

The display you are connecting must have an HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's U244-001-HDMI-R USB to HDMI adapter.

## VGA with Audio to HDMI Converter, Adapter for Stereo Audio and Video

MODEL NUMBER: **P116-000-HDMI**



Converts the VGA and Audio signal from a laptop or PC for use on a HDMI display

### Description

Tripp Lite's P116-000-HDMI VGA + Audio to HDMI converter is the perfect solution for using your older laptop or PC with your new HDMI display. Simply connect your computers VGA and Audio ports to the converter, and the converter to the HDMI port on your display, and you are ready to go. No software or drivers required. If your computer has only a 3.5 mm. Mini Stereo Audio jack, connect it to the converter using a 3.5 mm. to RCA adapter cable such as Tripp Lite's P314-006. You can also convert the RGB Video and Stereo Audio signals on your DVD player, DVR, etc., for use on your HDMI display (Component Video to VGA adapter required) Furthermore, you reduce your equipment costs by eliminating the need to upgrade your computer's video card.

The P116-000-HDMI supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024. Supports 24-bit True Color (8-bits per channel), and HDCP compliant.

### Features

- Connect your VGA laptop or PC to a HDMI display to enjoy high definition video and audio
- Convert the RGB Video and Stereo Audio signals from your DVD player, DVR, etc., for use on a HDMI display (Component Video to VGA adapter required)
- Plug-and-Play, no software or drivers required
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Supports 24-bit True Color (8 bits per channel)
- Reduce equipment cost by eliminating the need to update your computer's video card

### Highlights

- Connect your VGA laptop or PC to a HDMI display to enjoy HD video and audio
- Convert RGB Video and Stereo Audio signals for use on a HDMI display
- Plug-and-play operation with no software required for easy, immediate installation
- Supports HD video resolutions up to 1080p, and computer video resolutions up to 1280 x 1024
- Reduce equipment cost by eliminating the need to update your computer's video card

### System Requirements

- The display you are connecting must have a HDMI port that can accept a converted HDMI signal. Contact your display manufacturer to confirm that it will work with a VGA + Audio to HDMI converter. If your display does not support this, an alternative solution is Tripp Lite's U244-001-VGA-R USB to HDMI adapter.
- Computer with a VGA Video and 3.5 mm. or RCA Audio Jacks (If your computer has only a 3.5 mm. Mini Stereo Audio jack, you can use a 3.5 mm. to RCA adapter cable such as Tripp Lite's P314-006.
- DVD player, DVR, etc. with RGB Video and Stereo Audio jacks (Component video to VGA adapter required)
- **Supported PC Video Resolutions** - 640 x 480 @ 60Hz, 72Hz, 75Hz, 85Hz, 800 x 600 @ 56Hz, 60Hz, 72Hz, 75Hz, 85Hz, 1024 x 768 @ 60Hz, 70Hz, 75Hz, 80Hz, 85Hz, 1280 x 1024 @ 60Hz, 75Hz
- **Supported HD Video Resolutions** - 480i @ 60Hz, 480p @ 60Hz, 720p @ 60Hz, 1080i @ 60Hz, 1080p @ 60Hz

### Package Includes

- P116-000-HDMI VGA + Audio to HDMI Converter
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output:



5V, 2A, 4 ft.)

- Owner's Manual

## Specifications

| OVERVIEW                                       |   |
|--|---|
| UPC Code                                       | 037332180162  |
| Technology                                     | HDMI; VGA/SVGA; Stereo Audio                        |
| POWER  |   |
| External Power Supply Input Specs (V / Hz / A) | 100-240V/ 50/60Hz/ 0.35A                            |
| External Power Supply Output Specs (V / A)     | 5V / 2A   |
| External Power Supply Cord Length (ft.)        | 4.0   |
| DC Barrel Plug                                 | OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve |
| PHYSICAL                                       |   |
| Color  | Black   |
| Shipping Dimensions (hwd / cm)                 | 14.48 x 6.35 x 20.57                                |
| Shipping Dimensions (hwd / in.)                | 5.70 x 2.50 x 8.10                                  |
| Shipping Weight (kg)                           | 0.41  |
| Shipping Weight (lbs.)                         | 0.90  |
| Unit Dimensions (hwd / cm)                     | 3.18 x 8.89 x 6.99                                  |
| Unit Dimensions (hwd / in.)                    | 1.25 x 3.5 x 2.75                                   |
| Unit Weight (kg)                               | 0.18  |
| Unit Weight (lbs.)                             | 0.40  |
| ENVIRONMENTAL                                  |   |
| Operating Temperature Range                    | 32 to 158 F (0 to 70 C)                             |
| Storage Temperature Range                      | 14 to 176 F (-10 to 80 C)                           |
| Operating Humidity Range                       | 10 to 85% RH, Non-Condensing                        |
| Storage Humidity Range                         | 5 to 90% RH, Non-Condensing                         |
| CONNECTIONS                                    |   |
| Side A - Connector 1                           | HD15 (FEMALE)                                       |
| Side A - Connector 2                           | (2) RCA (FEMALE)                                    |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Side B - Connector 1                | HDMI (FEMALE)           |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>