

## 2-Port DB9 (RS-232) Serial PCI Card with 16550 UART, Full Profile

MODEL NUMBER: **PCI-D9-02**



Adds 2 DB9 serial ports to your PCI computer or server or replaces existing DB9 ports.

### Description

The PCI-D9-02 2-Port DB9 Serial PCI Card adds two DB9 serial ports to your computer or server. By adding the PCI-D9-02 to a computer with no DB9 ports or not enough of them, you can upgrade your DB9 capability without having to buy a new computer.

Perfect for home or office, the PCI-D9-02 supports data transfer rates up to 115.2 Kbps on each port. It easily installs inside your computer in just a few minutes. The standard bracket's interface is compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots. Allow the appropriate drivers to automatically install on your hard drive (a driver CD is included if they don't), and connect DB9 serial extension cables (such as Tripp Lite's P520-006) to the card's DB9 connectors.

The PCI-D9-02 is fully compliant with PCI Local Bus Specification Revision 2.3 and compatible with industrial standard 16550 UART. On-chip 256-byte depth FIFO in transmit and receive paths of each port. Supports hardware and software flow control; PCI IRQ sharing and PCI power management; 5-, 6-, 7-, 8- and 9-bit serial formats; Even, Odd, None, Space and Mark parity; and 1- or 2-stop bit operation.

### Features

#### Adds 2 DB9 (RS-232) Serial Ports to Your Computer

- Upgrades your DB9 capability without buying a new computer or server
- Each port supports data transfer rates up to 115.2 Kbps
- Perfect for home or office use

#### Easy to Install Inside Your Computer

- Compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots
- Appropriate drivers install to your hard drive automatically

### Highlights

- Each port supports data transfer rates up to 115.2 Kbps
- Complies with PCI Local Bus Specification Revision 2.3
- Compatible with universal 3.3V and 5V 32-bit PCI/PCI-X slots
- Compatible with industrial standard 16550 UART
- Works with Windows® and Linux®

### System Requirements

- Computer with available universal 3.3V and 5V 32-bit PCI/PCI-X slot
- Windows (XP and later) or Linux (2.6.x and later)

### Package Includes

- PCI-D9-02 2-Port DB9 Serial PCI Card with 16550 UART, Full Profile
- Driver CD
- Owner's manual



#### Loaded with the Latest Features

- Complies with PCI Local Bus Specification Revision 2.3
- Compatible with industrial standard 16550 UART
- On-chip 256-byte depth FIFO in transmit and receive paths of each port
- Supports hardware and software flow control
- Supports PCI IRQ sharing and PCI power management
- Supports 5-, 6-, 7-, 8- and 9-bit serial formats
- Supports Even, Odd, None, Space and Mark parity
- Supports 1- or 2-stop bit operation

## Specifications

OVERVIEW	
UPC Code	037332193681
INPUT	
Cable Length (ft.)	0
Cable Length (m)	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.00 x 5.00 x 5.80
Shipping Dimensions (hwd / cm)	2.54 x 12.70 x 14.73
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Color	Red
CONNECTIONS	
Ports	2
FEATURES & SPECIFICATIONS	
Technology	Serial (RS232)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>