

In some applications, a signal booster (Model Number: B120-000) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite DVI over Cat5 Extender (Model Number: B140-101X) in place of a 100 ft. DVI cable and signal booster. Note that Tripp Lite's DVI over Cat5 Extender products support DVI Single Link resolutions only.

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 100 ft. (30.5 m)

MODEL NUMBER: P560-100



Description

Tripp Lite's 100-ft. (30.5 m) DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- For use with Dual or Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster (B120-000) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332131065 |
| Technology | DVI |

Highlights

- For use with Dual or Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- DVI monitor
- CPU with DVI Dual Link capabilities

Package Includes

- 100-ft. (30.5 m) DVI Dual Link TMDS Cable (DVI-D M/M)

| | |
|--------------------------------------|---------------------------|
| Cable Type | Passive |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Length (ft.) | 100 |
| Cable Length (m) | 30.49 |
| Shipping Dimensions (hwd / in.) | 17.00 x 14.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 43.18 x 35.56 x 1.27 |
| Shipping Weight (lbs.) | 5.21 |
| Shipping Weight (kg) | 2.36 |
| Unit Dimensions (hwd / in.) | 0.000 x 0.000 x 0.000 |
| CONNECTIONS | |
| Side A - Connector 1 | DVI-D DUAL LINK (MALE) |
| Side B - Connector 1 | DVI-D DUAL LINK (MALE) |
| Latching or Gripping Connector | No |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |