



# High-Speed HDMI Flat Cable, Digital Video with Audio, UHD 4K (M/M), Black, 6 ft. (1.83 m)

### MODEL NUMBER: P568-006-FL



### Features

- Flat design for better manageability
- Flat conductors reduce crosstalk and inductance
- Creates a pure digital connection between HDMI-enabled HDTV display devices and HDMI-enabled digital video sources
- · Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- · Gold-plated connectors provide optimal signal transfer
- Premium double-shielded cable protects against outside noise (EMI/RFI)
- Impedance-matched twisted-pair construction reduces cross-talk and interference
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations
- Supports Ultra High Definition (UHD) 4 video resolutions

## **Specifications**

OVERVIEW		
UPC Code	037332137975	
Product Type	Passive Cable	
Technology	НДМІ	
Cable Type	Passive	
VIDEO		
Max Supported Video Resolution	3840 x 2160 (4K) @ 30Hz	
Max Supported Color Depth	24-bit True Color	

### **Highlights**

- Premium double-shielded digital audio/video cable
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- High Speed HDMI and HDCP compliant
- Supports Ultra High Definition (UHD) 4K video resolutions

#### **Package Includes**

 6-ft Flat High Speed HDMI Gold Cable





r		
HDR Support	No	
3D Video Supported	No	
Chroma Sub Sampling	4:4:4	
EDID Support	Yes	
Signal Transmission	Bidirectional	
AUDIO		
Audio Specification	Stereo Audio	
CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	HDMI (MALE)	
Connector Plating	Gold	
Contact Plating	Gold	
Connector Style	Straight	
Latching or Gripping Connector	No	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	0	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5 mm	
Wire Gauge (AWG)	30	
Cable Length (ft.)		
	6	
Cable Length (m)	6 1.83	
Cable Length (m) Cable Length (in.)		
	1.83	
Cable Length (in.)	1.83 72	
Cable Length (in.) Ferrite Core	1.83 72 No	
Cable Length (in.) Ferrite Core Minimum Bend Radius	1.83   72   No   55mm	
Cable Length (in.) Ferrite Core Minimum Bend Radius Shipping Dimensions (hwd / in.)	1.83   72   No   55mm   7.00 x 9.00 x 0.50	





ENVIRONMENTAL	ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)		
Storage Temperature Range	-40° to 176°F (-40° to 80°C)		
Operating Humidity Range	10% to 85% RH, Non-Condensing		
Storage Humidity Range	5% to 90% RH, Non-Condensing		
COMMUNICATIONS			
Consumer Electronics Control (CEC) Supported	Yes		
FEATURES & SPECIFICATIONS			
EMI/RFI Line Noise Protection	No		
MST Support	No		
Antibacterial	No		
IP68 Rated	No		
IP20 Rated	No		
Armored Cable	No		
Ethernet Support	No		
HDCP Specification	1.3		
STANDARDS & COMPLIANCE			
Product Compliance	RoHS; REACH		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	Lifetime limited warranty		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.