

8K HDMI Fiber Active Optical Cable (AOC) - 8K UHD @ 60 Hz, HDR, Detachable Connector, M/M, Black, 20 m (66 ft.)

MODEL NUMBER: P568FM-20M-8K6



8K fiber cable transmits enhanced UHD 8K video with Dynamic HDR and 4:4:4 color in home theater and digital signage applications.

Features

HDMI Cable Helps Your Gaming, Home Theater or Digital Signage Setup Get 8K-Ready

This HDMI cable (M/M) securely connects laptops, tablets, PCs, Blu-ray players, game consoles or satellite/cable TV boxes to HDTVs, HD monitors, projectors or home theater receivers. Because the cable uses optical fiber, it can transmit HDMI signals longer distances with no latency or loss. It also eliminates any EMI/RFI line noise that can interfere with your audio/video signal and disrupt the performance of your connected equipment.

Enjoy the Clarity of 8K Video with 7.1-Channel Surround Sound and 4:4:4 Color

The P568FM-20M-8K6 supports UHD 8K video resolutions, 36-bit Deep Color, Dolby 7.1-channel surround sound and bandwidth up to 48 Gbps. It supports HDR (High Dynamic Range), providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 encryption allows you to stream 4K Amazon and Netflix content with no complications. This cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Take Advantage of the Most Advanced HDMI Features for Premier Picture Quality

This 8K-ready cable allows your compatible hardware to deliver up-to-date HDMI features, such as eARC (enhanced Audio Return Channel), which passes full-resolution surround sound signals to your speakers without compressing them. QMS (Quick Media Switching) switches from one frame rate to another without the delay of a blank screen between them. ALLM (Auto Low Latency Mode), VRR (Variable Refresh Rate) and QFT (Quick Frame Transport) reduce latency, refresh rate and lag for a more vivid gaming experience.

Advanced Fiber Cable Is Easier to Install than Copper

Because the fiber cable is slimmer and more flexible than standard copper HDMI cables, the P568FM-20M-8K6 is easier to install around corners and in hard-to-reach spaces behind equipment. Easily pull this AOC through 3/4" conduit utilizing the detachable connector. In addition, drill smaller holes if routing cable through walls or surfaces. It draws power from the connected device, so no external power supply is needed to transmit the HDMI signal across the longer distances unique to fiber optic cabling. **Note:** The cable must be installed in the correct direction to function properly, so please check the Source and Display labels on the connectors before installation.

Highlights

- Supports UHD resolutions up to 8K @ 60 Hz (4:4:4) for enhanced video without latency
- Detachable Micro-HDMI adapter for source end helps you pull cable through 3/4" conduit
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Fiber optic strands transmit audio/video over longer distances than standard copper
- Dispels EMI/RFI line noise that can disrupt A/V signal and affect equipment performance

System Requirements

- Both source and display devices must be compatible with HDMI 2.1 standards to access HDMI 2.1 features
- Both source and display devices must be compatible with 8K standards to watch 8K video

Package Includes

P568FM-20M-8K6 HDMI Fiber Active Optical Cable, M/M, Black, 20 m (66 ft.)



Powering Business Worldwide

TRIPP LITE
SERIES

Invest in Quality Construction for Reliable Performance

You're expecting this 8K cable to last a long time, which is why it has been constructed with high-quality materials. Contacts are gold-plated to resist corrosion. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord. A removable HDMI (Type A) to Micro-HDMI (Type D) adapter for the source end is included to allow you to easily pull the cable through conduit.

Specifications

OVERVIEW	
UPC Code	037332284495
Product Type	Active Optical Cable (AOC)
Technology	HDMI
Cable Type	Active
VIDEO	
Video Input	HDMI (MALE)
Video Output	HDMI (MALE)
Max Supported Video Resolution	7680 x 4320 60Hz
Max 1280 x 720 (720p) Range (ft)	65
Max 1920 x 1080 (1080p) Range (ft)	65
Max 1920 x 1200 Range (ft)	65
Max 2560 x 1600 Range (ft)	65
Max 3840 x 2160 (4K@30Hz) Range (ft)	65
Max 3840 x 2160 (4K@60Hz) Range (ft)	65
Max 4096 x 2160 (4K) Range (ft)	65
Max 5120 x 2880 (5K) Range (ft)	65
Max 7680 x 4320 (8K@30Hz) Range (ft)	65
Max 7680 x 4320 (8K@60Hz) Range (ft)	65
Signal Range (ft)	65
Signal Range (m)	20
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	65
Maximum Signal Range (m)	20



Powering Business Worldwide

TRIPP LITE
SERIES

Signal Transmission	Unidirectional
DisplayPort Alt Mode	No
AUDIO	
Audio Specification	DOLBY TRUE HD/DTS-HD
CONNECTIONS	
Side A - Connector 1	HDMI (MALE); MICRO HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	CMP; VW-1
Cable Outer Diameter (OD)	4.8mm
Wire Gauge (AWG)	30/28/25
Cable Length (ft.)	65
Cable Length (m)	19.82
Cable Length (in.)	780
Minimum Bend Radius	48mm
Number of Displays	1
Form Factor/Mounting Options	Cable
Unit Dimensions (hwd / in.)	9.250 x 2.910 x 8.860
ENVIRONMENTAL	
Operating Temperature Range	14° to 131°F (-10° to 55°C)
Storage Temperature Range	-13° to 158°F (-25° to 70°C)
Relative Humidity	10% to 80% RH, Non Condensing
Operating Humidity Range	10% to 85% RH, NON-CONDENSING
Storage Humidity Range	5% to 90% RH, NON-CONDENSING



Powering Business Worldwide

TRIPP LITE
SERIES

COMMUNICATIONS	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
FEATURES & SPECIFICATIONS	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Armored Cable	No
HDCP Specification	1.4; 2.2; 2.3
Driver Required	No
DIN Mountable	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 94
Product Compliance	CE (Europe); FCC (USA); RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.