

## DisplayPort Cable with Latching Connectors (M/M), 8K 60 Hz, HDR, HBR3, 4:4:4, HDCP 2.2, 9 ft. (2.7 m)

MODEL NUMBER: **P580-009-8K6**



8K DisplayPort cable connects your source and display devices to transmit enhanced 8K Ultra HD audio/video with HDR and 4:4:4 chroma.

### Features

#### DisplayPort 1.4 Cable Gets Your Gaming, Home Theater or Digital Signage Setup 8K-Ready

This high-speed DisplayPort (DP) cable (M/M) securely connects source and display devices compatible with DP 1.4 audio/video signals. Backward compatible with all your existing DisplayPort devices, including Blu-ray players, game consoles and 4K televisions, the P580-009-8K6 is ideal for future-proofing your high-definition or Ultra HD application in anticipation of an 8K upgrade.

#### Enjoy the Clarity of 4K/8K Video with Multi-Channel Audio and 4:4:4 Color

The P580-009-8K6 supports 8K Ultra HD resolutions up to 7680 x 4320 at 60 Hz with multi-channel sound. It's compatible with DisplayPort 1.4 standards for HDR, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks. HDCP 2.2 compliance allows you to stream 4K content with no complications. This BT.2020-compatible cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

#### Invest in Quality Construction for Reliable Performance

You're expecting this 8K cable to last a long time, which is why it has been constructed with high-quality materials, such as a rugged PVC jacket. Contacts and connectors are gold-plated to resist corrosion. The male connectors latch securely to help prevent the cable from becoming accidentally disconnected and disrupting a continuous audio/video signal. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the DisplayPort cord.

## Specifications

OVERVIEW	
UPC Code	037332254122
Product Type	Passive

### Highlights

- Supports UHD resolutions up to 8K @ 60 Hz (4:4:4) for state-of-the-art video quality
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Complies with HDCP 2.2 standards to display up-to-date 4K video content
- Plug-and-play operation with no software required for easy, immediate installation

### System Requirements

Both source and display devices must be compatible with 8K standards to watch 8K video

### Package Includes

P580-009-8K6 DisplayPort 1.4 Cable (M/M), 8K 60 Hz, 9 ft. (2.7 m)

Technology	DisplayPort
Cable Type	Passive
<b>VIDEO</b>	
Max Supported Video Resolution	7680 X 4320 60HZ (8K)
Max Supported Color Depth	24-bit True Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
EDID Support	Yes
Signal Transmission	Bidirectional
<b>INPUT</b>	
Bus Powered	Yes
<b>PHYSICAL</b>	
Color	Black
Material of Construction	PVC
Cable Jacket Color	Black
Connector Color	Blue
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	6.8MM
Wire Gauge (AWG)	30
Cable Length (ft.)	9
Cable Length (m)	2.74
Cable Length (in.)	108
Ferrite Core	No
Shipping Dimensions (hwd / in.)	9.50 x 7.00 x 0.75
Shipping Weight (kg)	0.18
Unit Dimensions (hwd / in.)	9.500 x 7.000 x 0.750
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Operating Humidity Range	0% TO 90% RH, NON-CONDENSING
Storage Humidity Range	0% TO 90% RH, NON-CONDENSING

<b>COMMUNICATIONS</b>	
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Connector Plating	Gold
Contact Plating	Gold
Connector Style	Straight
Latching or Gripping Connector	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
EMI/RFI Line Noise Protection	No
Integrated/Removable Cable	No
MST Support	No
Antibacterial	No
IP68 Rated	No
IP20 Rated	No
Fully Molded Connector Ends	No
Ohms	No
Integral Strain Relief	No
Impedance-Matched Twisted-Pair Construction	No
Scaler Function	No
IP67 Rated	No
Displayport Specification	1.4
HDCP Specification	2.2
DIN Mountable	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	IEC/EN 62040
Product Compliance	RoHS; CE (Europe); REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.