



# Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 4K 60 Hz, HDCP 2.2, 20 ft. (6.1 m)

MODEL NUMBER: P586-020-HD-V2A











HDCP 2.2-compliant cable connects the Mini DisplayPort (mDP) or Thunderbolt port on your PC, Mac or tablet to a 4K-enabled HDMI monitor, projector or television.

#### **Description**

The P586-020-HD-V2A Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M) connects an mDP- or Thunderbolt-enabled PC, Mac or tablet (such as the Surface Pro series) to the HDMI port on a 4K monitor, projector or television. With an mDP male connector on one end and a gold-plated high-grip HDMI male connector on the other, this cable requires no separate power adapter. It lets you continue using an existing 4K HDMI display without the extra expense of buying a new mDP monitor. Recommended for displaying crystal-clear video on a large monitor or digital sign, this cable supports UHD video resolutions up to 4K at 60 Hz (3840 x 2160) as specified in HDMI 2.0. The P586-020-HD-V2A also supports rich, full audio (if your DisplayPort card supports audio passthrough) and the latest HDCP 2.2 (High-Bandwidth Digital Content Protection) standards.

Because it's an active adapter, the 20-foot (6.1-meter) P586-020-HD-V2A is compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output. It's perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

The corrosion-resistant gold-plated HDMI connector and contacts provide maximum conductivity and minimize data loss. Its special high-grip plug prevents a loose or accidentally disconnected cable from causing picture loss. Integral strain relief with ridges on each end gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

### **Features**

**Send UHD Mini DisplayPort 1.2a Signals to a 4K HDMI Display**Connects mDP or Thunderbolt PC, Mac or tablet to a 4K-enabled HDMI monitor, projector or HDTVRecommended for displaying video on a large monitor or digital signmDP and high-grip HDMI male connectorsNo separate power adapter required

**Vibrant Video Quality**Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0Supports EDID specificationsActive adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort outputRecommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

Superior Materials for Superior PerformanceGold-plated HDMI connector and contacts for maximum conductivity and minimum data lossSpecial high-grip HDMI plug prevents accidental disconnectionsIntegral strain relief provides cable and connectors with flexibility and reduces stress

# **Specifications**

## **Highlights**

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Compliant with latest HDCP 2.2 standards
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections
- Supports EDID specifications

### **Package Includes**

 P586-020-HD-V2A Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 20 ft.





OVERVIEW		
UPC Code	037332200693	
Product Type	Active Cable	
Technology	HDMI; DisplayPort	
Cable Type	Active	
VIDEO		
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz	
Max Supported Color Depth	8-bit	
HDR Support	Yes	
CONNECTIONS		
Side A - Connector 1	MINI DISPLAYPORT (MALE)	
Side B - Connector 1	HDMI (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
PHYSICAL		
Color	Black	
Material of Construction	ABS, PVC	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.0 +/- 15mm	
Wire Gauge (AWG)	32	
Cable Length (ft.)	20	
Cable Length (m)	6.10	
Cable Length (in.)	240	
Shipping Dimensions (hwd / in.)	0.50 x 6.30 x 12.00	
Shipping Dimensions (hwd / cm)	1.27 x 16.00 x 30.48	
Shipping Weight (lbs.)	0.80	
Shipping Weight (kg)	0.36	
ENVIRONMENTAL		
Operating Temperature Range	32° to 104°F (0° to 40°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	10% to 90%, Non-Condensing	





Storage Humidity Range	10% to 90%, Non-Condensing	
FEATURES & ORFOLEIOATIONS		
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
Displayport Specification	1.2a	
HDCP Specification	2.2	
STANDARDS & COMPLIANCE		
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	
Product Warranty Period (U.S. & Canada)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.