


M.2 NGFF SSD (B-Key) to 2.5 in. SATA Open-Frame Housing Adapter

MODEL NUMBER: P960-001-M2-NE



M.2 SSD to SATA adapter increases performance of your 2.5 in. SATA application when connected to an M.2 NGFF SATA SSD drive.

Features

SSD to SATA Adapter Improves Performance of Your SATA Computer This adapter converts your M.2 NGFF SSD drive into a 2.5-inch SATA SSD for use with a standard SATA-enabled computer. The open-frame P960-001-M2-NE supports mount drive heights of 2242, 2260 and 2280, as well as data transfer rates up to 6 Gbps. Adding an M.2 NGFF SSD to your application can reduce your computer's power consumption and boost performance.

Open-Frame Housing Helps Keep the Intricate Electronic Components Cool The open frame is designed for maximum heat dissipation, keeping the adapter cool to boost its performance potential. To share data, simply connect the SATA drive to the M.2 NGFF connector and then the SATA connector to your computer's SATA port.

Just Plug and Play for Immediate Use Right Out of the Package No software, drivers or external power supply is required. Mounting hardware is included. The P960-001-M2-NE is compatible with all major operating systems, including Windows, Mac and Linux.

Highlights

- Connects 2242, 2260 and 2280 M.2 SATA SSD drives to your 2.5 in. SATA application
- Shares data at rapid transfer speeds up to 6 Gbps (SATA I/II/III)
- Open-frame housing provides maximum airflow to keep electronics cool
- Works with all major operating systems, including Windows, Mac and Linux
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Access old data or back up new data on an M.2 NGFF SSD using a SATA-enabled computer

System Requirements

- SATA host device
- B-Key or B+M Key M.2 NGFF SATA drive
- PCIe drives not supported

Package Includes

- P960-001-M2-NE M.2 NGFF SSD to 2.5 in. SATA Open-Frame Housing Adapter
- Mounting hardware
- Screwdriver
- Owner's manual

Specifications



UPC Code	037332242600
Drives Supported	2242, 2260, 2280 M.2 NGFF SSD
Technology	SATA/eSATA
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Yellow (Data & Power)
PHYSICAL	
Color	Green
Shipping Dimensions (hwd / in.)	1.10 x 4.80 x 6.10
Unit Dimensions (hwd / in.)	0.28 x 3.92 x 2.76
Unit Weight (kg)	0.05
Unit Weight (lbs.)	0.11
ENVIRONMENTAL	
Operating Temperature Range	50 to 122°F (10 to 50°C)
Storage Temperature Range	32 to 149°F (0 to 65°C)
Relative Humidity	10% to 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	M.2 NGFF SATA (B-Key)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS and REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>