

2-Port Gigabit Ethernet PCI Express (PCIe x4) Network Interface Card (NIC), I350-T2

MODEL NUMBER: PCE-1G-02-NIC



Adds 2 Gigabit Ethernet RJ45 ports to a computer's motherboard via a 4-lane PCI Express (PCIe) slot.

Features

Adds Dual Gigabit Ethernet Ports to Your Desktop Computer

The high-performance PCE-1G-02-NIC connects to your desktop computer's motherboard and adds two 10/100/1000 Mbps RJ45 ports via an available four-lane PCI Express (PCIe) slot. Based on the bridgeless Intel I350 controller, this adapter is a 1 Gbps networking innovation for enterprise and data center applications. Add multiple Ethernet ports to dual-homed proxy or gateway systems for added security and redundant connectivity for uninterrupted network connections.

Recommended for VM Environments

This PCIe network interface card (NIC) is ideal for Virtual Machine (VM) environments with multiple operating systems that require shared or dedicated NICs. It also is a valuable addition to desktop PC servers and workstations with few PCIe slots available in which turning one RJ45 port into two is beneficial.

Loaded with the Latest Features

The PCE-1G-02-NIC supports common IEEE standards, including 802.3ab (1000Base-T Gigabit Ethernet), 802.3u (100base-TX), 802.3az, 802.1Q (VLAN) and 802.1ad. The high-performing bridgeless design supports PCI Express Gen 2.1 5GT/s x4, compatible with PCIe x8 or x16.

Innovative Power Management Features for Enterprise and Data Centers

Energy Efficient Ethernet (EEE) and DMA coalescing increase efficiency and reduce power consumption for enterprise and data center applications. Scalable iSCSI performance delivers cost-effective SAN connectivity. The PCE-1G-02-NIC also supports jumbo frames, VMDq, DPDK, PXE, WOL and FCoE. Flexible I/O virtualization is ideal for port partitioning and quality of service (QoS) of up to 32 virtual ports.

Installs in Minutes

The halogen-free adapter is compatible with copper UTP cabling, including 1000Base-T Cat5e/Cat6 or higher up to 100 meters, 100Base-Tx Cat5/Cat5e/Cat6 or higher up to 100 meters, and 10Base-T Cat3/4/5/5e/6 or higher up to 100 meters. The PCE-1G-02-NIC can be installed with either a standard or low-profile bracket (both are included).

Specifications

Highlights

- Adds two 1G network ports to a single four-lane PCI Express slot in a desktop PC
- Based on Intel I350 chipset for superior functionality in complex network applications
- Compliant with IEEE 802.ab, 802.3u, 802.3 az, 802.1Q and 802.1ad
- Includes a low-profile mounting bracket for low-profile PC builds
- Compatible with Windows and Linux operating systems

System Requirements

- Requires an available PCI Express (PCIe) x4/x8/x16 slot
- Compatible with Windows and Linux operating systems

Package Includes

- PCE-1G-02-NIC 2-Port Gigabit Ethernet Network Card
- Low-profile bracket
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

| OVERVIEW | |
|-------------------------------------|--|
| UPC Code | 037332286390 |
| Technology | PCIe |
| CONNECTIONS | |
| Number of Ports | 2 |
| PHYSICAL | |
| Color | Green |
| Shipping Dimensions (hwd / in.) | 1.06 x 6.18 x 4.92 |
| Shipping Dimensions (hwd / cm) | 2.69 x 15.70 x 12.50 |
| Shipping Weight (lbs.) | 0.15 |
| Shipping Weight (kg) | 0.07 |
| Unit Dimensions (hwd / in.) | 4.720 x 2.720 x 4.650 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 131F (0 to 55C) |
| Storage Temperature Range | -40 to 158F (-40 to 70C) |
| Operating Humidity Range | 35% to 90%, non-condensing |
| STANDARDS & COMPLIANCE | |
| Product Compliance | CE (Europe); FCC (USA); IEEE 802.1q Tagged VLAN; IEEE 802.3 10Base-T; IEEE 802.3ab 1000Base-T; IEEE 802.3ad (LACP); IEEE 802.3az (Energy Efficient Ethernet); IEEE 802.3u 100Base-TX/FX; IEEE 802.3x Flow Control; IEEE 802.3z 1000Base-SX/LX; REACH; RoHS; UKCA |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.