


14.5kW 3-Phase Monitored PDU LX Interface, 208/240V Outlets (42 C13/6 C19), LCD, Hubbell CS8365C, 1.8m/6 ft. Cord, 0U 1.8m/70 in. Height, TAA

MODEL NUMBER: PDU3EVN6H50B



14.5kW 3-phase PDU with network interface and multifunction touchscreen LCD distributes and monitors AC power in an IT or industrial environment.

Description

The PDU3EVN6H50B 14.5kW 3-Phase Monitored PDU provides real-time remote monitoring of voltage, frequency and load levels via built-in network connection. By reducing the frequency of on-site visits, these advanced remote capabilities can save you money and reduce downtime.

A color touchscreen LCD lets you toggle between menus to monitor input current level per phase and output current per load bank with $\pm 1\%$ billing-grade accuracy, environmental sensor data and network information. It also generates a unique QR code to allow access to the PDU through a mobile device.

Recommended for IT and industrial applications, this PDU features 42 C13 and 6 C19 receptacles with included plug-lock insert sleeves to prevent cables from becoming accidentally disconnected. A six-foot cord with Hubbell CS8365C input plug connects the PDU to a compatible AC power source, generator or protected UPS.

The 0U PDU mounts vertically in racks using the included toolless mounting buttons or the included rack-mounting brackets. Use the included PDUMVROTATEBRKT kit to install the unit with outlets facing the rear for better airflow or equipment access.

A built-in Java-free HTML5-based LX Platform network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities. LX Platform supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network.

Features

Distributes and Monitors Network-Grade AC Power 14.5kW 208/240V monitored PDU with 3-phase input Hubbell CS8365C plug with 6 ft. cord connects to compatible AC power source Firmware upgrades support future product enhancements

48 Receptacles Distribute AC Power 42 C13 and 6 C19 outlets split into 3 separately breakered load banks Plug-lock insert sleeves prevent cables from becoming accidentally disconnected

Color Touchscreen LCD Reports network data, including IP address, input current level per phase and output current per load bank with $\pm 1\%$ billing-grade accuracy Generates unique QR code for read-only access to PowerAlert® Device Manager via mobile device Full access available by logging into PowerAlert

Highlights

- 14.5kW 208/240V 3-phase monitored 0U PDU
- 42 C13 and 6 C19 receptacles with plug-lock inserts
- 6 ft. AC power cord with Hubbell CS8365C input
- Built-in LX Platform interface for remote access 24/7
- Touchscreen LCD with mobile access option via QR code

Package Includes

- PDU3EVN6H50B 14.5kW 3-Phase Monitored PDU
- Configuration cable
- (48) Plug-lock insert sleeves
- Rack-mounting hardware
- PDUMVROTATEBRKT mounting bracket accessory
- Owner's manual



Device Manager via browser as user with read/write credentials
Built-In Java-Free HTML5-Based LX Platform Interface Allows full remote access for power monitoring with email notifications via secure web browser, SNMP, telnet or SSH Supports 10/100 Mbps auto-sensing for communication with an Ethernet network Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities
Broad Communications Compatibility Supports IPv4, IPv6, HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP Supports automatic and manual assignment of IP address
Easy 0U Installation in EIA-Standard 19 in. Racks Mounts vertically using included toolless buttons or rack-mounting brackets Included PDUMVROTATEBRKT allows mounting with rear-facing outlets
TAA-Compliant Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332195340
PDU Type	Monitored
INPUT	
PDU Input Voltage	208; 240
Recommended Electrical Service	50A 208/240V with Hubbell CS8365C outlet
Maximum Input Amps	35
PDU Plug Type	HUBBELL CS8365C 50A
Input Phase	3-Phase
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity Details	14.5kW (240V), 12.6kW (208V) total capacity; 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(42) C13; (6) C19
Output Nominal Voltage	208; 240
Overload Protection	3 20A circuit breakers, 1 per outlet bank
USER INTERFACE, ALERTS & CONTROLS	
Reported Load Segments	Reports input current per phase (L1, L2, L3) and output current for each breakered load bank (20A balanced max per banks B1-B3); Outlets are color-coded and labeled for phase and load bank identification; L1-L2 feeds black outlets (B1); L2-L3 feeds dark-gray outlets (B2); L3-L1 feeds light-gray outlets (B3)
Front Panel LCD Display	Touchscreen LCD reports NETWORK DATA (IP address, Subnet Mask, Gateway, MAC Address, Device Name, Model, Serial Number), INPUT PHASE DATA (Amperage, Wattage, Voltage per phase, plus Unbalance percentage), LOAD BANK DATA (Amperage, Wattage, Voltage per load bank, plus total PDU output in watts), CONFIGURATION DATA (Listing of current configuration settings), ENVIRONMENTAL DATA (Reports data and status of E2 sensor modules; Sensor options are available for temperature and humidity, plus input and output dry contacts), MOBILE ACCESS (Generates a unique QR code to view reported PDU details on a mobile device)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Current Measurement Accuracy (Amps)	+/-1%
Voltage Measurement Accuracy (Volts)	+/-1%
Power Measurement Accuracy (Watts)	+/-1%
PHYSICAL	
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	15.75 x 24.89 x 191.77
Shipping Dimensions (hwd / in.)	6.20 x 9.80 x 75.50
Shipping Weight (kg)	10.85
Shipping Weight (lbs.)	23.92
Unit Dimensions (hwd / cm)	177.8 x 5.5 x 7.3
Unit Dimensions (hwd / in.)	70 x 2.17 x 2.86
Unit Weight (kg)	7.78
Unit Weight (lbs.)	17.15
ENVIRONMENTAL	
Operating Temperature Range	32 to 122F (0C to 50C)
Storage Temperature Range	-30°C to +60°C (-22°F to +140°F)
Relative Humidity	5 to 95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Pre-installed LX platform network interface
SPECIAL FEATURES	
High Availability PDU Features	Auto Probe Monitoring (included)
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA) CAN/CSA 60950-1 (Canada), NOM (Mexico), FCC Class A Part 15 (Emissions), ROHS, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>