

3.7kW Single-Phase Metered PDU, 208/230V Outlets (8 C13, 2 C19) IEC-309 16A Blue, 8 ft. (2.43 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH16HV



Highlights

- Metered single phase 16A 208/230V PDU
- 1U horizontal rackmount; digital current meter
- C20 input with IEC-309 Blue 16A input; 2.5m line cord
- 10 total outlets (8 C13, 2 C19); 6.5 in. / 16.5 cm depth
- TAA Compliant

Package Includes

- Rackmount PDU
- Rack mounting brackets
- Plug lock inserts
- IEC-309 Blue 16A input cord

Features

- 3.7kW 16A single phase 208/230V Metered Power Distribution Unit / PDU
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with IEC-309 Blue 16A input; 2.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Front panel grounding lug
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332182791
PDU Type	Metered
INPUT	
PDU Input Voltage	208/230V
Recommended Electrical Service	Single-phase 16/20A 230/208V service



Maximum Input Amps	16
PDU Plug Type	IEC-309 16A BLUE (2P+E)
Input Phase	Single-Phase
Input Cord Length (ft.)	8.2
Input Cord Length (m)	2.50
OUTPUT	
Output Capacity Details	3.7kW (230V), 3.3kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13; (2) C19
Output Nominal Voltage	208/230V
Overload Protection	n/a
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
Material of Construction	Metal
Minimum Required Rack Depth (cm)	25.40
Minimum Required Rack Depth (inches)	10
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	7.70 x 51.99 x 27.79
Shipping Dimensions (hwd / in.)	3.03 x 20.47 x 10.94
Shipping Weight (kg)	2.95
Shipping Weight (lbs.)	6.50
Unit Dimensions (hwd / cm)	2.87 x 44.4 x 16.5
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 6.5
Unit Weight (kg)	3.08
Unit Weight (lbs.)	6.8
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
TVSS Grounding	Front panel grounding lug
STANDARDS & COMPLIANCE	
Certifications	Class A (Emissions), CE (IEC / EN60950-1), GOST, RoHS compliant, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>