

# TAA Compliant 3-Phase Local Metered PDU, 14.4kW, 45 208V outlets (36 C13, 6 C19, 3 L6-30R), 6-ft. Hubbell CS8365C 50A plug

MODEL NUMBER: PDU3MV6H50ATAA



## Description

Tripp Lite 3 phase Local Metered PDU / Power Distribution Units offer real-time local reporting of current levels in amps via set of 3 built-in digital meters. Enables visual monitoring of PDU current levels to preserve proper loading balance and prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

## Features

- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases
- 14.4kW 3 phase 208V Local Metered Power Distribution Unit / PDU
- Set of 3 built-in current meters continuously report load current in amps for all 3 output phases
- Attached Hubbell CS8365C 50A (3P+E) 208V 3 phase input plug with 6 ft. / 1.8m cord
- 0U, 70 in. / 178cm vertical form factor supports installation in 2 or 4 post equipment racks
- 45 total 208V outlets (36 C13, 6 C19, 3 L6-30R) arranged in three breakered single phase output load banks
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)

## Highlights

- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases
- Local Metered 14.4kW 3 Phase 208V PDU; 70 in. / 178cm 0U vertical rackmount
- Reports load current per-phase via set of 3 built-in current meters
- Hubbell CS8365C 50A (3P+E) 208V 3 phase input; 6 ft. / 1.8m line cord
- 45 208V outlets total (36 C13, 6 C19, 3 L6-30R)
- Toolless button-mount installation; cord retention brackets included

## Package Includes

- TAA Version of Tripp Lite PDU3MV6H50A
- Cord retention brackets
- Spare installation buttons (2 9mm / 4 6mm)
- Rack mounting brackets
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332273338



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

PDU Type	Local Metered
<b>INPUT</b>	
Input Phase	3-Phase
PDU Input Voltage	208V
Maximum Input Amps	40
Maximum Input Amps Details	Agency de-rated to 40A continuous
PDU Plug Type	HUBBELL CS8365C 50A
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
<b>OUTPUT</b>	
Output Capacity Details	14.4kVA total; Bank L1-L2: 30A max, Bank L2-L3: 20A max, Bank L3-L1: 20A max
Frequency Compatibility	60 Hz
Output Nominal Voltage	208V single phase
Overload Protection	3 double-pole circuit breakers (Breaker L1-L2 30A - protects 3 L6-30R outlets / Breaker L2-L3 20A - protects 18 C13 and 3 C19 outlets / Breaker L3-L1 20A - protects 18 C13 and 3 C19 outlets)
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>PHYSICAL</b>	
Material of Construction	Steel
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
Unit Dimensions (hwd / in.)	70.000 x 2.650 x 1.730
Unit Dimensions (hwd / cm)	177.8 x 6.7 x 4.39
Unit Weight (lbs.)	14.5
Unit Weight (kg)	6.58
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-30°C to +60°C (-22°F to +140°F)
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10,000
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.