


3-Phase Metered PDU, 8.6 kW, 45 208V outlets (36 C13, 9 C19), 6 ft. (1.83 m) NEMA L21-30P Input connection, TAA Compliant

MODEL NUMBER: PDU3MV6L2130A



Features

- 8.6kW 3 phase 208V Metered Power Distribution Unit / PDU
- Set of 3 built-in current meters continuously report load current in amps for all 3 output phases
- Attached NEMA L21-30P (3P+N+E) 208V 3 phase input plug with 6 ft. / 1.8m cord
- 0U, 70 in. / 178cm vertical form factor supports installation in 2 or 4 post equipment racks
- 45 total 208V outlets (36 C13, 9 C19) arranged in three breakered single phase output load banks
- Included cord retention sleeves keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications (set of 2 9mm buttons pre-installed, 2 9mm and 4 6mm spare buttons included)
- TAA Compliant

Highlights

- Metered 8.6kW 3 Phase 208V PDU; 70 in. / 178cm 0U vertical rackmount
- Reports voltage and load per-phase via set of 3 digital current displays
- NEMA L21-30P (3P+N+E) 208V 3 phase input, 6-ft. (1.83 m) line cord
- 45 208V outlets (36 C13, 9 C19) with included plug-lock cord retention sleeves
- Toolless button-mount installation, TAA Compliant

Package Includes

- Metered PDU with pre-installed mounting buttons
- Cord retention sleeves (36 C14, 9 C19)
- Spare installation buttons (2 9mm / 4 6mm)
- Rack mounting brackets
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332182746
PDU Type	Metered
INPUT	
PDU Input Voltage	208V
Recommended Electrical Service	Three-phase 30A 208V service



Maximum Input Amps	24
PDU Plug Type	NEMA L21-30P
Input Phase	3-Phase
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity Details	8.6kW (208V) total capacity; 13.9A max per output phase (L1-L2, L2-L3, L3-L1), 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(36) C13; (9) C19
Output Nominal Voltage	208V
Overload Protection	3 20A double-pole circuit breakers (1 per output phase)
USER INTERFACE, ALERTS & CONTROLS	
Reported Load Segments	Supports local monitoring of current for each output phase (13.8A balanced max per output load bank L1-L2, L2-L3 and L3-L1); Outlets are color coded and labeled for phase and load bank identification; L1-L2 feeds black outlets; L2-L3 feeds dark-gray outlets; L3-L1 feeds light-gray outlets
Front Panel LCD Display	Set of 3 digital current meters report output current per phase
Front Panel LEDs	n/a
Switches	n/a
PHYSICAL	
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	18.01 x 24.51 x 192.71
Shipping Dimensions (hwd / in.)	7.09 x 9.65 x 75.87
Shipping Weight (kg)	10.31
Shipping Weight (lbs.)	22.72
Unit Dimensions (hwd / cm)	177.8 x 6.73 x 5.6
Unit Dimensions (hwd / in.)	70 x 2.65 x 2.2
Unit Weight (kg)	6.12
Unit Weight (lbs.)	13.50
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Relative Humidity	5 to 95% non-condensing
STANDARDS & COMPLIANCE	
Certifications	Tested to UL/CSA60950-1 (USA, Canada), NOM (Mexico), Class A (Emissions), ROHS, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>