

# TAA-Compliant 5/5.8kW Single-Phase Local Metered PDU, 208/240V Outlets (16-C13 & 2-C19), L6-30P, 12ft Cord, 2U Rack-Mount

MODEL NUMBER: PDUMH30HVTAA



## Description

Tripp Lite single phase Local Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital current metering. Enables visual monitoring of PDU output current to preserve proper output balance and prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

## Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 30A single phase 208/240V Local Metered Power Distribution Unit / PDU (Agency derated to 24A continuous)
- Set of two lighted meters report PDU output current in amps for each 9 outlet load bank
- Attached NEMA L6-30P 30A 208/240V input plug and 12ft / 3.6m cord
- 2U horizontal rackmount format installs in two rack spaces
- 18 output receptacles (16 C13, 2 C19)
- Outlets are arranged in two 9 outlet load banks, each with separate 20A breaker and current metering
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Cord retention brackets keep vital equipment plugs connected
- Grounding lug

## Specifications

### Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- Local Metered single phase 30A 208/240V 2U horizontal rackmount PDU
- Two built-in meters report output current in amps for each load bank
- Attached 12ft / 3.6m cord with NEMA L6-30P input plug
- 18 total outlets (16 C13, 2 C19)
- Reversible housing, 2U 208/240V rackmount local metered PDU

### Package Includes

- TAA Compliant version of Tripp Lite PDUMH30HV
- Mounting brackets
- Plug retention plates
- User manual



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

UPC Code	037332273314
PDU Type	Local Metered
<b>INPUT</b>	
Input Phase	Single-Phase
Recommended Electrical Service	30A 208/240V
Maximum Input Amps	30
Maximum Input Amps Details	Agency de-rated to 24A continuous
PDU Plug Type	NEMA L6-30P
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
<b>OUTPUT</b>	
Output Capacity Details	5.8kW (240V), 5kW (208V), 4.8kW (200V) total capacity / 30A max (Agency de-rated to 24A), 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13; (2) C19
Output Nominal Voltage	200; 208; 240
Overload Protection	Two 20A breakers protect 9 outlets each
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Set of 2 digital meters continuously report output current for breakered load banks 1 & 2 (Bank 1: upper row of 9 outlets / Bank 2: lower row of 9 outlets)
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>PHYSICAL</b>	
Material of Construction	Steel
Form Factors Supported	2U rackmount; mounting accessories included
PDU Form Factor	Horizontal (1U)
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 12.500
Unit Dimensions (hwd / cm)	8.8 x 44.4 x 31.8
Unit Weight (lbs.)	13.7
Unit Weight (kg)	6.21
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)

Relative Humidity	0-95% non-condensing
Operating Elevation	0-10,000
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.