

TAA-Compliant 7.4kW Single-Phase Local Metered PDU, 230V Outlets (2-C19, 16-C13), IEC-309 230V 32A Blue 12ft Cord, 2U Rack-Mount

MODEL NUMBER: PDUMH32HVTAA



Description

Tripp Lite Local Metered Power Distribution Units / PDU systems continuously report output load level in amps to help network managers prevent overloads and plan for future growth. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. Highly reliable design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 32A single phase 230V Local Metered Power Distribution Unit / PDU
- Set of two lighted current meters separately report power consumption in amps for each output load bank
- Attached IEC-309 32A (2P+E) input plug with 12 ft. / 3.6m line cord
- 2U horizontal rackmount format installs in two rack spaces
- 18 total 230V outlets (2 C19, 16 C13)
- Outlets are arranged in two separately breakered and local metered 16A load banks (each with 8 C13 and 1 C19 outlet)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Front-panel grounding lug
- Included cord retention brackets

Specifications

OVERVIEW	
UPC Code	037332273321

Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- Local Metered single phase 32A 230V 2U horizontal rackmount PDU
- Set of 2 current meters reports current in amps for each output load bank
- Attached 12 ft. / 3.6m cord with IEC-309 32A (2P+E) input plug
- 18 total 230V outlets (2 C19, 16 C13)
- Reversible housing, 12.5 in. / 31.75cm depth

Package Includes

- TAA Compliant version of Tripp Lite PDUMH32HV
- Mounting brackets
- Plug retention brackets
- User manual



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
Nominal Input Voltage(s) Supported	230V AC
Maximum Input Amps	32
PDU Plug Type	IEC-309 32A BLUE (2P+E)
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	7.4kW (230V) / 32A total capacity / 16A max per breakered outlet bank; 16A max per C19 outlet; 10A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13; (2) C19
Output Nominal Voltage	230
Overload Protection	Two 20A circuit breakers protect 9 outlets each
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Set of 2 digital meters continuously report output current for breakered load bank; Bank 1 (Upper row of 9 outlets), Bank 2 (Lower row of 9 outlets)
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Steel
Form Factors Supported	2U rackmount
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 12.500
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 31.75
Unit Weight (lbs.)	13.7
Unit Weight (kg)	6.21
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)

Relative Humidity	0-95% non-condensing
Operating Elevation	0-10,000
FEATURES & SPECIFICATIONS	
High Availability PDU Features	Auto-Transfer Switching
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.