



3.2-3.8kW Single-Phase Monitored PDU, 200-240V Outlets (20-C13, 4-C19), C20/L6-20P, 0U Vertical, 70 in., TAA

MODEL NUMBER: PDUMNV20HV



Description

Tripp Lite Monitored PDU / Power Distribution Unit offers real-time remote monitoring of voltage, frequency and load levels via built-in network connection. PowerAlert interface supports custom notification of user-specified remote conditions via email, PowerAlert Console Launcher, SNMP, Telnet or SSH interface. PDU output current consumption in amps is displayed via front panel lighted digital display and can be monitored remotely to warn of potential overloads before critical IT mains breakers trip.

Features

- 200/208/230/240V Monitored PDU with built-in network interface in 0U 70 in. / 178cm rackmount form factor; 20A maximum capacity (agency de-rated to 16A)
- C20 inlet supports user supplied input cabling; 10ft / 3m L6-20P power cord included
- 24 outlets (20 C13 & 4 C19)
- 0U 70in / 178cm vertical rackmount form factor
- Network interface provides PDU control and data regarding input voltage, frequency and loading information
- Digital display reports load level information in amps
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- · Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- · Tiered access privileges allow an administrator and a guest to login simultaneously
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols

Highlights

- Monitored 16/20A 200-240V PDU; 0U 70in / 178cm vertical rackmount
- Reports voltage, frequency and load level via ethernet interface
- Visual current meter, Toolless button-mount installation
- C20 inlet, 10ft / 3m L6-20P power cable included
- 24 outlets (20 C13 & 4 C19) with included cord retention brackets
- Temperature, humidity and contact-closure monitoring options
- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases

Package Includes

- Rackmount PDU
- · Plug retention plates
- · Rack mounting brackets
- Owner's manual





- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications
- Federal Trade Agreements Act / TAA compliant for GSA schedule purchases

Specifications

| OVERVIEW | |
|--------------------------------|---|
| UPC Code | 037332149534 |
| PDU Type | Monitored |
| INPUT | |
| Input Phase | Single-Phase |
| Recommended Electrical Service | 20A 208/240V; 16A 230V |
| Maximum Input Amps | 20 |
| Input Connection Type | C20 inlet accepts included L6-20P input cable. Alternate C19 input cordsets supported. |
| PDU Plug Type | NEMA L6-20P; IEC-320 C20 |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 3.05 |
| OUTPUT | |
| Output Capacity Details | 3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (20) C13; (4) C19 |
| Output Nominal Voltage | 200; 208; 220; 230; 240 |
| USER INTERFACE, ALERTS & CO | NTROLS |
| Front Panel LCD Display | Digital meter reports PDU output current in amps, Scroll IP-address information; Display can be rotated 180 degrees for installation with the input cable at the top |
| Switches | Press the SCROLL IP / ROTATE button and release after one second to display the configured IP address in 2 digit intervals; Press and release after two seconds to rotate the display 180 degrees |
| SURGE / NOISE SUPPRESSION | |
| Automatic Shut-Off | No |
| PHYSICAL | |
| Form Factors Supported | 0U vertical rackmount installation supported with included mounting brackets; supports tooless mounting in button- mount compatible racks |
| PDU Form Factor | Vertical (0U) |





| Shipping Dimensions (hwd / in.) | 4.00 x 6.00 x 72.50 |
|--|--|
| Shipping Dimensions (hwd / cm) | 10.16 x 15.24 x 184.15 |
| Shipping Weight (lbs.) | 13.50 |
| Shipping Weight (kg) | 6.12 |
| Unit Dimensions (hwd / in.) | 70.000 x 2.190 x 2.650 |
| Unit Dimensions (hwd / cm) | 177,8 x 5,6 x 6,7 |
| Unit Weight (Ibs.) | 8.50 |
| Unit Weight (kg) | 3.86 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0C ~ 40C (32F ~ 104F) |
| Storage Temperature Range | 5 to 122F (-15 to 50C) |
| Relative Humidity | 5-95% non-condensing |
| Operating Elevation | 0-10,000 |
| COMMUNICATIONS | |
| PowerAlert Software | LX Platform Interface: PowerAlert Device Manager |
| Communications Cable | RJ45-to-DB9 configuration/console Access cable |
| SNMP Compatibility | Pre-installed SNMPWEBCARD provides remote monitoring via PowerAlert Console Launcher, Telnet, SSH, and SNMP management systems |
| Network Compatibility | 10 Mbps; 100 Mbps (Fast Ethernet) |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.