

## 1.4kW Single-Phase Switched PDU, 120V Outlets (16 5-15R), 5-15P, 10ft Cord, 0U Vertical, 49 in, TAA Compliant, TAA

MODEL NUMBER: PDUMV15NET



### Description

Tripp Lite single phase Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is continuously displayed locally via visual meter and remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

### Features

- 120V Switched PDU with built-in web/network interface in 0U 49in / 124cm vertical rackmount form factor; 15A maximum capacity (Agency derated to 12A continuous)
- Attached NEMA 5-15P 120V single phase input plug with 10 ft. / 3m input cord
- 16 switched NEMA 5-15R outlets
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and total output load level in amps
- Digital display continuously reports output load in amps
- Display also supports IP-address self-identification and 180 degree display rotation
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors

### Highlights

- Switched 15A 120V PDU, 0U 49 in. / 125cm vertical rackmount
- Reports voltage, frequency and load level via ethernet interface
- Visual current meter, Toolless button mount installation
- NEMA 5-15P input plug with 10 ft. / 3m line cord
- 16 switched NEMA 5-15R outlets with cord retention brackets
- Temperature, humidity and contact closure monitoring options
- TAA Compliant for GSA Schedule purchases

### Package Includes

- Rackmount PDU
- Rack mounting brackets
- PDUMVROTATEBRKT
- Owner's manual

- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332139702
PDU Type	Switched
INPUT	
Input Phase	Single-Phase
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) 5-15R
Output Nominal Voltage	100; 120; 127
Customized Load Management Receptacles	16 individually switched output receptacles
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	16 LEDs display power on-off status for each output receptacle
Switches	Pushbutton control supports 180 degree Display Rotation and Scroll IP address functions



Powering Business Worldwide



<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>PHYSICAL</b>	
Form Factors Supported	0U vertical rackmount. Includes mounting brackets. Supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	4.00 x 6.00 x 51.75
Shipping Dimensions (hwd / cm)	10.16 x 15.24 x 131.44
Shipping Weight (lbs.)	11.00
Shipping Weight (kg)	4.99
Unit Dimensions (hwd / in.)	49.000 x 2.190 x 2.650
Unit Dimensions (hwd / cm)	124.5 x 5.6 x 6.7
Unit Weight (lbs.)	7
Unit Weight (kg)	3.18
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation	0-10,000
<b>COMMUNICATIONS</b>	
PowerAlert Software	SNMPWEBCARD Interface: PowerAlert 12
Communications Cable	RJ45-to-DB9 configuration/console Access cable
SNMP Compatibility	Yes, pre-installed SNMPWEBCARD provides remote monitoring via web, telnet, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
Network Compatibility	10 Mbps; 100 Mbps (Fast Ethernet)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.