

3.7kW Single-Phase Local Metered PDU, 208/230V Outlets (6-C19 & 32-C13) C20/L6-20P Cable 10 ft. (3.05 m) Cord, 0U Vertical

MODEL NUMBER: PDUMV20HV



Features

- 16/20A single phase 230/208V Local Metered Power Distribution Unit / PDU (Agency derated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 0U 63.75in / 162cm vertical rackmount format installs using no rack spaces
- 38 total outlets (6 C19, 32 C13)
- Included plug-lock inserts ensure components remain connected and powered
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Highlights

- Local metered single phase 16A 208/230V 0U 63.75in / 162cm vertical rackmount PDU
- Two-digit meter reports output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 38 output receptacles (6 C19, 32 C13)
- Ready for immediate toolless 0U installation

Package Includes

- PDUMV20HV 63.75 inch basic PDU
- Plug-lock inserts (6 C20, 32 C13)
- Spare installation buttons, 2.9 mm/4.6 mm
- 10-ft. (3.05 m) detachable C19-to-L620P input cordset
- Mounting hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332139344
PDU Type	Local Metered
INPUT	
PDU Input Voltage	208; 230
Recommended Electrical Service	Single-phase 16/20A 230/208V service
Maximum Input Amps	16

Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	L6-20P detachable cordset, C20 inlet available
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Phase	Single-Phase
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	3.68kW (230V), 3.33kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(32) C13; (6) C19
Output Nominal Voltage	208/230V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Form Factors Supported	0u vertical installation in equipment racks, plus under-counter and wallmount
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	5.00 x 3.50 x 65.50
Shipping Dimensions (hwd / cm)	12.70 x 8.89 x 166.37
Shipping Weight (lbs.)	9.50
Shipping Weight (kg)	4.31
Unit Dimensions (hwd / in.)	3.750 x 2.250 x 63.750
Unit Dimensions (hwd / cm)	162 x 5.7 x 9.5
Unit Weight (lbs.)	5.20
Unit Weight (kg)	2.36
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	0-95% non-condensing
Operating Elevation (ft.)	0-10,000

Operating Elevation (m)	0-3000
STANDARDS & COMPLIANCE	
Product Certifications	IEC 62368-1; RETIE (Colombia); GOST (Russia); NOM (Mexico)
Product Compliance	RoHS; CE (Europe); EAC (Belarus, Kazakhstan, Russia); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty