


## 3.2–3.8kW Single-Phase Switched PDU with LX Platform Interface, 200–240V Outlets (20 C13 & 4 C19), C20/L6-20P, 0U, TAA

MODEL NUMBER: PDUMV20HVNETLX



3.2–3.8kW vertical PDU distributes, monitors and manages single-phase power in an IT or industrial environment. Built-in network interface helps you remotely monitor load levels to prevent overloads that cause downtime.

### Description

The PDUMV20HVNETLX 3.2-3.8kW Single-Phase Switched PDU provides advanced network control and remote power monitoring with the ability to turn on, turn off, reboot or lock out power to each outlet. Recommended for any IT or industrial application, it features 24 switched outlets (20 C13 and 4 C19) with included plug-lock insert sleeves to prevent cables from becoming accidentally disconnected. A 10-ft. (3.05 m) cord with NEMA L6-20P plug connects the PDU's C20 inlet to a compatible AC power source, generator or protected UPS.

The built-in Java-free HTML5-based LX Platform network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities. Protocols supported include HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP.

A digital ammeter allows you to monitor each bank's load in real time to ensure it remains well below maximum capacity with no danger of overload. The vertical PDU mounts in 0U of space in EIA-standard 19-inch racks using the included toolless mounting buttons or the included rack-mounting brackets. Use the included PDUMVROTATEBRKT kit to install the unit with outlets facing the rear for better airflow or equipment access.

### Features

**Distributes Network-Grade Single-Phase Power** 3.2-3.8kW 200/208/230/240V switched PDU Recommended for network applications requiring individual outlet control, load shedding and remote

### Highlights

- 3.2–3.8kW 200/208/230/240V switched PDU
- 24 individually controllable outlets—20 C13, 4 C19
- Pre-installed WEBCARDLX with latest version of PADM20 for IP-based Auto Probe feature
- Digital ammeter for on-site load monitoring in real time
- C20 inlet with 10ft NEMA L6-20P AC power cord

### Package Includes

- PDUMV20HVNETLX 3.2-3.8kW Single-Phase Switched PDU
- Built-in LX Platform interface
- Detachable NEMA L6-20P to C19 power cord, 10-ft. (3.05 m)
- Configuration cable
- (24) Plug-lock inserts
- Rack-mounting hardware
- PDUMVROTATEBRKT mounting bracket accessory
- Owner's manual



monitoring of critical network componentsIncludes detachable NEMA L6-20P plug with 10-ft. (3.05 m) cord; C20 inlet supports user-supplied international input cablingFirmware upgrades support future product enhancements

**24 Switched Outlets Distribute AC Power**20 C13 and 4 C19 outlets split into 2 separately breakered load banksIndividual outlets can be remotely controlled to power up, power down, reboot or lock out devicesPlug-lock inserts prevent cables from becoming accidentally disconnected

**Digital Ammeter**Reports load level on each bank and total PDU outputSupports IP-address self-IDRotates 180° for easy reading at either angle

**Built-In LX Platform Interface**Pre-installed WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilitiesPADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurationsIP-based Auto Probe detects lost connectivity and restores service autonomously

**Easy 0U Installation in EIA-Standard 19 in. Racks**Mounts vertically using included toolless buttons or rack-mounting bracketsIncluded PDUMVROTATEBRKT allows mounting with rear-facing outlets

**TAA-Compliant**Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332205292
PDU Type	Switched
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	20A 208/240V; 16A 230V
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	C20 inlet accepts included L6-20P input cable
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Phase	Single-Phase
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(20) C13; (4) C19
Output Nominal Voltage	200; 208; 220; 230; 240
Overload Protection	n/a
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface



<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Front Panel LEDs	24 power availability LEDs confirm power off/on status for each built-in outlet; LX Platform Interface status LED (Green); Network Link/Activity LED (Yellow), Network Speed LED (Green)
Switches	Push button to rotate digital display and view IP address. LX Platform Interface: Recessed reset switch for interface reboot and factory reset
<b>PHYSICAL</b>	
Form Factors Supported	0U vertical rackmount; includes rackmount brackets. Supports toolless mounting in button-mount compatible racks
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	13.46 x 16.26 x 185.42
Shipping Dimensions (hwd / in.)	5.30 x 6.40 x 73.00
Shipping Weight (kg)	6.44
Shipping Weight (lbs.)	14.20
Unit Dimensions (hwd / cm)	177,8 x 5,6 x 6,7
Unit Dimensions (hwd / in.)	70 x 2.19 x 2.65
Unit Weight (kg)	3.86
Unit Weight (lbs.)	8.5
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-30°C to +60°C (-22°F to +140°F)
Relative Humidity	Up to 95% non-condensing
<b>COMMUNICATIONS</b>	
Network Monitoring Port	RJ45 Network port; RJ45 Config/Console Access port; USB A port supports a variety of Envirosense2 environmental and control modules. See Accessories>Management Hardware section for more information about these modules.
SNMP Compatibility	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems
<b>SPECIAL FEATURES</b>	
High Availability PDU Features	Auto Probe Monitoring and Reboot (included)
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL 60950-1:2007 (USA), CAN/CSA-C22.2 NO. 60950-1-07 (Canada), IEC 60950-1: 2005 (CE), FCC Class A, EN55022:2010+2011, EN55024:2010 (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>