


12-Outlet Vertical Power Strip, 120V, 20A, Hardwired Input, 36 in.

MODEL NUMBER: PS3612-20HW



Highlights

- AC input hardwired via knockout on unit
- 12 outlets
- 20-amp capacity
- Ideal for applications requiring permanent installation

Package Includes

- PS3612-20HW
- Instruction manual

Description

PS3612-20HW Power Strip offers 20A multi-outlet AC power distribution in a convenient 36-inch hardwire cabinet. Includes knockout panels to accept 3/4-inch conduit fittings for hardwire installation and 12 output receptacles with three-inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

Features

- Versatile all-metal 36 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 12 outlets total: 2 NEMA 5-15/20R (20A) and 10 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332042385
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	Hard-wire
Input Cord Length (ft.)	0



Powering Business Worldwide



Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(2) 5-15/20R; (10) 5-15R
Circuit Breaker (amps)	20
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
Outlet Spacing	2.99 in.
PHYSICAL	
Color	Beige
Material of Construction	Metal
Housing Color	Beige
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	4 in.
Receptacle Color	Beige
Shipping Dimensions (hwd / in.)	2.50 x 2.60 x 41.00
Shipping Dimensions (hwd / cm)	6.35 x 6.60 x 104.14
Shipping Weight (lbs.)	3.65
Shipping Weight (kg)	1.66
Unit Dimensions (hwd / in.)	1.500 x 1.500 x 36.000
Unit Dimensions (hwd / cm)	91.44 x 3.8 x 3.8
Outlet Spacing	2.99 in.
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.