

12-Outlet Vertical Power Strip, 120V, 20A, Hardwired Input, 36 in.

MODEL NUMBER: **PS3612-20HW**



Highlights

- AC input hardwired via knockout on unit
- 12 outlets
- 20-amp capacity
- Ideal for applications requiring permanent installation

Package Includes

- PS3612-20HW
- Instruction manual

Description

Tripp Lite's PS3612-20HW Power Strip offers 20 amp multi-outlet AC power distribution in a convenient 36 inch hardwire cabinet. Includes knockout panels to accept 3/4 in. conduit fittings for hardwire installation and 12 output receptacles with 2.99 inch center-to-center spacing. Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications.

INPUT/OUTPUT: Input: Hardwire access via knockout panels that accept 3/4 inch conduit fittings

Output: 12 Outlets total (2 NEMA 5-15/20R and 10 NEMA 5-15R)

ELECTRICAL: 120V AC, 50/60Hz, 20A (no circuit breaker)

FORMAT: 36 inch strip format

Features

- Versatile all-metal 36 inch format with outlets arranged in a single row
- Knockout panels for 3/4 inch conduit fittings allow permanent hardwire installation
- Ideal for horizontal or vertical raceway style power distribution in office, workbench, industrial, networking and telecom applications
- 12 outlets total: 2 NEMA 5-15/20R (20A) and 10 NEMA 5-15R (15A)
- 20 amp electrical capacity
- 120VAC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
UPC Code	037332042385
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V

Voltage Compatibility (VAC)	120
Input Plug Type	Hard-wire
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) 5-15/20R; (10) 5-15R
Circuit Breaker (amps)	20
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
Outlet Spacing	2.99 in.
PHYSICAL	
Color	Beige
Material of Construction	Metal
Housing Color	Beige
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	101.60mm
Receptacle Color	Beige
Shipping Dimensions (hwd / in.)	2.50 x 2.60 x 41.00
Shipping Dimensions (hwd / cm)	6.35 x 6.60 x 104.14
Shipping Weight (lbs.)	3.65
Shipping Weight (kg)	1.66
Unit Dimensions (hwd / in.)	1.500 x 1.500 x 36.000
Unit Dimensions (hwd / cm)	91.44 x 3.8 x 3.8
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty