

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

For Patient-Care Vicinity - UL 1363A Medical-Grade Power Strip, 4 Hospital-Grade Outlets, 10 ft. Cord, Drip Shield

MODEL NUMBER: PS410HGOEMX



Power strip with built-in cord manager and optional drip shield supplies power to movable plug-connected components mounted to IV poles, carts and mobile medical workstations inside or outside of patient-care vicinities.

Description

The PS410HGOEMX Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria, such as C. diff and MRSA, and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The built-in cord wrap provides easy cord management in mobile applications. The drip shield can be mounted for extra protection when there are liquids in the environment.

Mounting tabs and flanges let you install the PS410HGOEMX on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies

Highlights

- Patented antimicrobial coating
99.9% effective in inhibiting bacteria and viruses
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 10 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Optional drip shield provides extra protection from liquids

Package Includes

- PS410HGOEMX UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets, 10 ft. Cord, Cord Wrap and Drip Shield
- Owner's Manual with maintenance requirements



with UL 1363A specifications

Exclusive, Patented Antimicrobial ProtectionSilver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria like C. diff and MRSA Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution4 NEMA 5-15R-HG hospital-grade outlets provide consistent power Integrated cord wrap provides easy cord management Rugged, all-metal housing for long life in demanding environments

Premium Safety FeaturesDual, resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shut-off Drip shield adds extra measure of safety against liquids and moisture

Ready to Use Right Out of the BoxBuilt-in mounting tabs and flanges make the PS410HGOEMX easy to install on a variety of surfaces

Specifications

OVERVIEW	
UPC Code	037332168948
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch



PHYSICAL	
Antimicrobial Coating	Yes
Cable Management	Bar
Color	White
Color (AC Line Cord)	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Included Mounting Accessories	Mounting tabs and flanges
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Material of Construction	Metal
Receptacle Color	White
Shipping Dimensions (hwd / cm)	25.70 x 15.49 x 5.99
Shipping Dimensions (hwd / in.)	10.12 x 6.10 x 2.36
Shipping Weight (kg)	1.39
Shipping Weight (lbs.)	3.06
Unit Dimensions (hwd / cm)	25.25 x 10.8712 x 5.51
Unit Dimensions (hwd / in.)	9.94 x 4.28 x 2.17
Unit Weight (kg)	1.29
Unit Weight (lbs.)	2.84
SPECIAL FEATURES	
Built-in Cable Management	Yes
STANDARDS & COMPLIANCE	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>