

# TAA-Compliant 3.2-3.8kW Single-Phase Local Metered PDU, 200-240V (8-C13 & 2-C19), C20/L6-20P Adapter, 12ft Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH20HVTAA



### Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- Local Metered single phase 16/20A 200-240V PDU
- 1U horizontal rackmount; digital current meter
- C20 input with L6-20P plug adapter; 12 ft. / 3.7m line cord
- 10 total outlets (8 C13, 2 C19)
- Reversible housing; 6.5 in. / 16.5 cm depth

### Package Includes

- TAA Compliant version of Tripp Lite PDUMH20HV
- C19 to L6-20P plug adapter
- Rack mounting brackets

### Description

Tripp Lite Local Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital meter. Enables visual current monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 16/20A single phase 200-240V Local Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with C20 input cable and L6-20P adapter; 12 ft. / 3.7m line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks  
Back panel grounding lug

## Specifications

OVERVIEW	
UPC Code	037332273284
PDU Type	Local Metered

INPUT	
Input Phase	Single-Phase
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	3.3kW (208V input), 3.5kW (220V input), 3.7kW (230V input), 3.8kW (240V input), 3.2kW (200V input); 20A maximum (Agency de-rated to 16A continuous)
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13; (2) C19
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	Outlets are arranged in a single unbreakered load bank
Customized Load Management Receptacles	Each outlet is individually controllable via remote interface
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Steel
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
PDU Form Factor	Horizontal (1U)
Unit Dimensions (hwd / in.)	1.750 x 17.500 x 6.500
Unit Dimensions (hwd / cm)	2.87 x 44.4 x 16.5
Unit Weight (lbs.)	6.8
Unit Weight (kg)	3.08
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10,000
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.