

UL1363a, Paragraph 14.1(d) states, "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

For Patient Care Vicinity - UL 1363A Medical-Grade Power Strip, 4 Hospital-Grade Outlets, 15 ft. (4.57 m) Right-Angle Cord

MODEL NUMBER: PS-415-HG-OEMRA



Delivers power to devices attached to IV poles, crash carts and mobile workstations in operating rooms and other patient care vicinities.

Features

4-Outlet Medical-Grade Power Strip with Long 15 ft. Cord Approved for Patient Care Vicinities Tripp Lite's PS-415-HG-OEMRA supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations inside and outside patient care vicinities when properly mounted. This includes operating rooms, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V power strip features four NEMA 5-15R-HG hospital-grade outlets.

Exclusive, Patented Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs) The power strip is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria, such as C. diff and MRSA, and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Premium Safety Features Help Ensure Proper Power Connections With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Two resettable 15-amp circuit breakers will shut down all AC input if the power strip determines the connected equipment load is drawing too much power. Four locking plastic safety covers are included to block access to unused outlets.

Ready for Installation in Demanding Medical Environments The power strip with 15-ft. (4.57 m) cord also includes a space-saving right-angle NEMA 5-15P-HG plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. Built-in mounting flanges and integrated keyhole slots let you install the durable all-metal housing on any mobile cart or IV pole for distributing power to movable rack-, table- and pedestal-mounted equipment.

Highlights

- UL 1363A power strip for use inside and outside patient care vicinities
- Patented antimicrobial coating 99.9% effective in inhibiting bacteria and viruses
- Right-angle 5-15P-HG plug permits connection in confined or hard-to-reach spaces
- 15-ft. (4.57 m) power cord allows flexibility in placing power strip in relationship to AC outlet
- Switchless design helps prevent accidental shutdown of essential equipment

Applications

- Supply safe medical-grade power to lab, imaging and other electric components mounted to an IV pole or crash cart in a patient care area

Package Includes

- PS-415-HG-OEMRA Medical-Grade Power Strip, 4 Outlets, 15-ft. (4.57 m) Cord
- (4) Outlet safety covers
- Owner's manual

Specifications

OVERVIEW



UPC Code	037332239389
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Right-Angle Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Antimicrobial Coating	Yes
Color	White
Color (AC Line Cord)	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Included Mounting Accessories	mounting flanges and integrated keyhole slots
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	White
Shipping Dimensions (hwd / cm)	6.10 x 24.64 x 16.00
Shipping Dimensions (hwd / in.)	2.40 x 9.70 x 6.30
Shipping Weight (kg)	1.32
Shipping Weight (lbs.)	2.90
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Dimensions (hwd / in.)	8.65 x 2.5 x 1.5
Unit Weight (kg)	1.02
Unit Weight (lbs.)	2.25
SPECIAL FEATURES	
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Approvals	TUV tested to UL 1363A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>