

## Safe-IT UL 2930 Medical-Grade Power Strip for Patient-Care Vicinity, 4 15A Hospital-Grade Outlets, Safety Covers, 15 ft. Cord

MODEL NUMBER: PS-415-HGULTRA



Full UL 2930 compliance, integrated locking safety covers and a 15 ft. cord make this medical-grade power strip ideal for all areas inside and outside of patient care vicinities.

### Description

The PS-415-HGULTRA Medical-Grade Power Strip is UL 2930 compliance and agency listing, making it ideal for standalone use in all patient care vicinities. This 120V, 60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

PEGT, External Grounding Terminal provides a redundant path to ground for medical equipment. This reduces the risk of electric shock in case of insulation failure or ground fault.

The power strip is protected by an antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew.

Mounting tabs and flanges let you install the PS-415-HGULTRA on a wide variety of surfaces. Aluminum housing ensures safety and is guaranteed to last a long time in demanding environments.

With a switchless design that prevents accidental shutoff and a 15-foot (4.6-meter) power cord that can reach a distant power source, the PS-415-HGULTRA is a recommended replacement for all non-compliant power strips.

### Features

**Power Distribution Anywhere in Any Medical Facility** Ideal for standalone use in patient care vicinities, therapy rooms, imaging environments and administrative areas  
Patented protection circuit guards against shock hazards with automatic site fault protection  
120V 60 Hz power strip complies with UL 2930 specifications  
Access product specifications instantly with QR code integration ensuring critical documentation is available when and where it's needed

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew

**Versatile Medical-Grade Solution** 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power  
15 ft. (4.57 m) power cord provides ample reach to the power source  
Aluminum housing for long life in demanding environments

**Premium Safety Features** Integrated locking outlet safety covers block access to unused outlets  
PEGT,

### Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for standalone use in all patient care vicinities
- Complies with UL 2930 and NFPA 99 specifications
- 4 NEMA 5-15R-HG hospital-grade outlets with locking safety covers

### Package Includes

- PS-415-HGULTRA UL 2930 Medical-Grade Power Strip
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

External Grounding Terminal provides a redundant path to ground for medical equipment  
Switchless design prevents accidental shut-off

**Ready to Use Right Out of the Box** Built-in mounting tabs and flanges for easy installation on a variety of surfaces

## Specifications

OVERVIEW	
UPC Code	037332128430
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V/125V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge (AWG)	12GA, 3 COND, SJT
Voltage Compatibility (VAC)	120; 125
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Output Receptacles	(4) 5-15R-HG
Overload Protection	15A
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No Power Switch
LED Indicators	GREEN LED INDICATES POWER
PHYSICAL	
Color	White
Material of Construction	Aluminum
Power Cord Color	White



Powering Business Worldwide

TRIPP LITE  
SERIES

Housing Color	White
Mounting Holes or Slots	Yes
Outlets Measurement (Center to Center)	81.6MM
Receptacle Color	White
Shipping Dimensions (hwd / in.)	13.19 x 6.50 x 0.50
Shipping Dimensions (hwd / cm)	33.50 x 16.51 x 1.27
Shipping Weight (lbs.)	3.24
Shipping Weight (kg)	1.47
Unit Dimensions (hwd / in.)	11.020 x 2.500 x 1.790
Unit Dimensions (hwd / cm)	28 X 6.35 X 4.45
Unit Weight (lbs.)	2.69
Unit Weight (kg)	1.22
Mounting Details	MOUNTING BRACKET AND KEYHOLES
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Grounding Details	PEGT, External Ground Terminal (UL2930 requirement)
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 2930
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.