

Standards that govern use of this product vary by country and sometimes municipality. In the United States, this product is not for use in the Patient Care Vicinity, as defined in the National Electric Code (NEC). This product is approved to CSA C22.2/CuL standards and approved for use in Canada. For application guidance and product selection in your country, please consult a [Tripp Lite Healthcare Product Specialist](#) or your own expert.

UL 1363 Medical-Grade Power Strip, 6 Hospital-Grade Outlets, Antimicrobial, 15 ft. (4.57 m) Cord

MODEL NUMBER: **PS-615-HG**



Delivers power to devices outside of patient care vicinities, including therapy rooms and administrative areas.

Features

6-Outlet Power Strip Supplies Power Outside Patient Care VicinitiesThis medical-grade power strip is for administrative areas or resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. This includes operating rooms, therapy rooms, imaging environments and administrative areas. With six NEMA 5-15R-HG outlets and a 15-ft. (4.57 m) power cord with NEMA 5-15P-HG plug, this 120V power strip complies with UL 1363.

Exclusive, Patented Antimicrobial Protection Fights Healthcare-Acquired Infections (HAIs)The PS-615-HG is protected by a patented antimicrobial powder coating with EPA-registered and FDA-compliant silver ionic technology. The antimicrobial surface protection is 99.9 percent effective in inhibiting the growth of bacteria, such as C. diff and MRSA, and reducing the risk of HAIs in hospitals and other medical environments. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Premium Safety Features Help Ensure Proper Power ConnectionsWith no central power switch, the PS-615-HG presents no danger of accidental shutoff and cutting off power to essential devices. One resettable 15-amp circuit breaker shuts down all input if the connected load draws too much power.

Ready for Installation Straight from the BoxBuilt-in mounting flanges and integrated keyhole slots let you install the durable metal housing on any wall or other flat surface for distributing immediate power to equipment outside a patient care vicinity.

Highlights

- UL 1363 power strip for use outside patient care vicinities
- Patented antimicrobial coating 99.9% effective in inhibiting bacteria and viruses
- NEMA 5-15P-HG plug permits connection in confined or hard-to-reach spaces
- 15-ft. (4.57 m) power cord allows flexibility in placing power strip in relationship to AC outlet
- Switchless design helps prevent accidental shutdown of essential equipment

Applications

Supply safe medical-grade power to lab, imaging and other electric components outside a patient care area

Package Includes

- PS-615-HG Medical-Grade Power Strip
- Owner's manual

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332100108 |
| INPUT | |



| | |
|--|---|
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Input Plug Features | Hospital Grade Plug |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P-HG |
| Input Cord Length (ft.) | 15 |
| Input Cord Length (m) | 4.57 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (6) 5-15R-HG |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A circuit breaker |
| Transformer Accommodation | (2) Yes |
| Outlet Orientation | Single row of 6 |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | No power switch |
| PHYSICAL | |
| Antimicrobial Coating | Yes |
| Color | White |
| Color (AC Line Cord) | White |
| Included Mounting Accessories | Keyhole mounting tabs and flanges |
| Integrated Keyhole Mounting Slots | Yes (Includes flanges) |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm |
| Material of Construction | Metal |
| Outlets Measurement (Center to Center) | 38.7mm |
| Receptacle Color | White |
| Shipping Dimensions (hwd / cm) | 5.08 x 14.73 x 35.81 |
| Shipping Dimensions (hwd / in.) | 2.00 x 5.80 x 14.10 |
| Shipping Weight (kg) | 1.50 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|-------------------------------------|
| Shipping Weight (lbs.) | 3.30 |
| Unit Dimensions (hwd / cm) | 3.8 x 34.9 x 6.4 |
| Unit Dimensions (hwd / in.) | 1.5 x 13.75 x 2.5 |
| SPECIAL FEATURES | |
| Built-in Cable Management | No |
| STANDARDS & COMPLIANCE | |
| Canada | cUL (Series Number: AGIB12015SL) |
| UL1363 (Power Tap) | UL1363 (Series Number: AGIB12015SL) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>