

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

For Patient-Care Vicinity - UL 1363A Medical-Grade Power Strip with 6 20A Hospital-Grade Outlets, 15-ft. Cord

MODEL NUMBER: **PS615HG20AOEM**



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care areas.

Description

The PS615HG20AOEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care areas, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-20P-HG hospital-grade plug and six NEMA 5-20R-HG hospital-grade outlets.

Anti-Microbial Protected with EPA Registered and FDA Compliant Silver Ionic Technology known to inhibit growth of Microbes on surfaces.

Two resettable built-in 20A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. Locking safety covers are integrated to protect unused outlets from debris and damage. Long 15-foot 20A AC power cord gives you flexibility to roll the equipment where it's most needed. Mounting tabs and flanges let you install the PS615HG20AOEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. All-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution in Any Medical Facility Ideal for operating rooms, administrative areas, patient-care areas, therapy rooms and imaging environments Attaches easily to IV poles, mobile carts, crash carts and mobile workstations 120V, 50/60 Hz power strip complies with UL 1363A specifications

Versatile Medical-Grade Solution Six NEMA 5-20R-HG hospital-grade outlets provide consistent power Long 15-foot 20A AC power cord with NEMA 5-20P-HG hospital-grade plug lets you move the components where power is most needed Rugged all-metal housing for long life in demanding environments

Premium Safety Features Dual resettable built-in 20A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff Integrated locking safety covers keep debris away from unused outlets

Highlights

- Approved for use in patient-care areas when properly mounted
- Complies with UL 1363A specifications
- Features six NEMA 5-20R-HG hospital-grade outlets
- Features 15-ft. cord with NEMA 5-20P-HG hospital-grade plug
- Mounts on a wide variety of surfaces
- Exclusive, patented anti-microbial coating - 99.9% effective in inhibiting bacteria and viruses

Package Includes

- PS615HG20AOEM UL 1363A Medical-Grade Power Strip with 6 20A Hospital-Grade Outlets
- Owner's Manual with maintenance requirements



Ready to Use Right from the Box Mounting tabs and flanges let you install the unit on a wide variety of surfaces

Exclusive, Patented Antimicrobial Protection Silver ionic powder coating is 99.9% effective in inhibiting the growth of bacteria like C. diff and MRSA Patented coating helps to reduce the risk of healthcare-acquired infections (HAIs) in hospitals and other medical environments Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Specifications

OVERVIEW	
UPC Code	037332190680
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(6) 5-20R-HG
Circuit Breaker (amps)	20
Overload Protection	2 x 20amp breaker (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A, 120V
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Anti-Microbial Protected	Yes
Color	White
Color (AC Line Cord)	White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between end tabs = 330.20mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	38.7mm
Receptacle Color	White
Shipping Dimensions (hwd / cm)	17.81 x 10.21 x 37.39
Shipping Dimensions (hwd / in.)	7.01 x 4.02 x 14.72
Shipping Weight (kg)	1.96
Shipping Weight (lbs.)	4.32
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Dimensions (hwd / in.)	13.75 x 2.5 x 1.5
Unit Weight (kg)	1.02
Unit Weight (lbs.)	2.25
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>