

## Important Note

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

## Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x 20A Hospital-Grade Outlets, 15 ft. (4.57 m) Cord

MODEL NUMBER: PS615HG20AOEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care areas.

## Description

The PS615HG20AOEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care areas, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-20P-HG hospital-grade plug and six NEMA 5-20R-HG hospital-grade outlets.

The power strip is protected by a antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two resettable built-in 20A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. Locking safety covers are integrated to protect unused outlets from debris and damage.

Long 15-foot (4.6-meter) 20A AC power cord gives you flexibility to roll the equipment where it's most needed. Mounting tabs and flanges let you install the PS615HG20AOEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. All-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

## Features

**Power Distribution in Any Medical Facility** Ideal for operating rooms, administrative areas, patient-care areas, therapy rooms and imaging environments Attaches easily to IV poles, mobile carts, crash carts and mobile workstations 120V, 50/60 Hz power strip complies with UL 1363A specifications

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Versatile Medical-Grade Solution** Six NEMA 5-20R-HG hospital-grade outlets provide consistent

## Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care areas when properly mounted
- Complies with UL 1363A and NFPA 99 specifications
- Features six NEMA 5-20R-HG hospital-grade outlets
- Features 15 ft. (4.6 m) cord with NEMA 5-20P-HG hospital-grade plug

## Package Includes

- PS615HG20AOEM UL 1363A Medical-Grade Power Strip with 6 20A Hospital-Grade Outlets
- Owner's Manual with maintenance requirements



Powering Business Worldwide

TRIPP LITE  
SERIES

powerLong 15 ft. (4.6 m) 20A AC power cord with NEMA 5-20P-HG hospital-grade plug lets you move the components where power is most neededRugged all-metal housing for long life in demanding environments

**Premium Safety Features**Dual resettable built-in 20A circuit breakers protect against dangerous overloadsSwitchless design prevents accidental shutoffIntegrated locking safety covers keep debris away from unused outlets

**Ready to Use Right from the Box**Mounting tabs and flanges let you install the unit on a wide variety of surfaces

## Specifications

OVERVIEW	
UPC Code	037332190680
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(6) 5-20R-HG
Circuit Breaker (amps)	20
Overload Protection	2 x 20amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between end tabs = 330.20mm
Outlets Measurement (Center to Center)	1.52 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	7.01 x 4.02 x 14.72
Shipping Dimensions (hwd / cm)	17.81 x 10.21 x 37.39
Shipping Weight (lbs.)	4.32
Shipping Weight (kg)	1.96
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Weight (lbs.)	2.25
Unit Weight (kg)	1.02
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.