

1U Rack-Mount Power Strip, 120V, 15A, 5-15P, 12 Outlets (6 Front-Facing, 6-Rear-Facing), 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215



Highlights

- Designed for standard 19-inch racks (1U high)
- 12 outlets (6 front / 6 rear)
- 15-amp circuit breaker
- 15-ft. (4.57 m) cord

Package Includes

- RS-1215
- Mounting hardware
- Instruction manual

Description

Tripp Lite's RS-1215 Power Strip offers 15 amp capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-15R outlets (6 front/6 rear), 15-ft. (4.57 m) AC power cord and lighted switch with cover prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA 5-15P
Output: 12 NEMA5-15R (6 front & 6 rear)
ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)
FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 NEMA5-15R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord NEMA5-15P plug connection
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 15 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW

UPC Code	037332011534
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(5) Yes
Outlet Orientation	6 front facing / 6 rear facing
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Included Mounting Accessories	Rackmount flanges
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	Distance between Front outlets = 3.28 in.; Distance between Rear outlets = 4.5 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.00 x 9.30 x 20.50
Shipping Dimensions (hwd / cm)	5.08 x 23.62 x 52.07
Shipping Weight (lbs.)	5.57

Shipping Weight (kg)	2.53
Unit Dimensions (hwd / in.)	1.750 x 17.500 x 4.000
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Grounding	Back panel nut and bolt grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty