


Management Interface

The management interface for this PDU model is transitioning to a new technology platform. The new interface can be distinguished by a USB-A port (for EnviroSense2 modules) in place of the round ENVIROSENSE port. For managing the units containing the round port, Tripp Lite recommends using the [PowerAlert Console Launcher](#) rather than a web browser. This application enables local access of the PDU using a self-contained, compatible Java Runtime Environment version. The Console Launcher can be downloaded for free; click the above link or go to the Management Solutions / Utilities page. Units with the new interface work with most current web browsers.

5/5.8kW Single-Phase Monitored PDU with LX Platform Interface, 208/240V Outlets (12-C13 and 4-C19), L6-30P, 12ft Cord, 2U Rack-Mount, TAA

MODEL NUMBER: PDUMNH30HV



Description

Offers real-time remote monitoring of voltage, frequency and load levels via built-in network connection. The built-in Java-free HTML5-based LX Platform network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities. Protocols supported include HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP.

PDU lighted digital display enables visual monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 30A single phase 208/240V Monitored Power Distribution Unit / PDU (agency derated to 24A continuous)
- Attached NEMA L6-30P input with 10ft / 3m line cord
- 2U horizontal rack-mount format supports installation in 2 or 4 post equipment racks
- 16 outlets (12 C13, 4 C19)

Highlights

- Monitored 30A 208/240V PDU, 2U horizontal rackmount
- Reports voltage, frequency & load level via built-in LX Platform Interface
- Visual current meter, Reversible housing
- L6-30P input with 12ft / 3.6m line cord
- 16 outlets (12 C13, 4 C19) with included cord retention brackets
- Temperature, humidity and contact-closure monitoring options
- TAA Compliant

Package Includes

- Monitored PDU
- Built-in LX Platform interface
- Rack installation brackets
- Cable retention brackets
- Configuration cable
- Owner's manual



- Lighted display with select button reports output power consumption in amps in 3 segments (bank 1, bank 2 and total)
- LX Platform interface allows full remote access for power monitoring with email notifications via secure web browser, SNMP, telnet or SSH
- Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing allows optimal communication with 10/100 Base-T networks
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser for monitoring
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements.
- Supports HTTP, HTTPS, PowerAlert, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with free PowerAlert Network Management System software
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332159205
PDU Type	Monitored
INPUT	
PDU Input Voltage	200; 208; 240
Recommended Electrical Service	30A 208/240V
Maximum Input Amps	30
Maximum Input Amps Details	Agency de-rated to 24A continuous
PDU Plug Type	NEMA L6-30P
Input Phase	Single-Phase
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66



OUTPUT	
Output Capacity Details	5.8kW (240V), 5kW (208V), 4.8kW (200V) total capacity / 30A max (Agency de-rated to 24A), 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) C13; (4) C19
Output Nominal Voltage	200; 208; 240
Overload Protection	Two 20A breakers protect 8 outlets each
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital current meter reports PDU output current in amps for 3 loading segments (Bank 1, Bank 2 and Banks 1&2 combined)
Front Panel LEDs	Front panel LEDs indicates which loading segment the digital LCD current display is reporting; Bank 1 LED indicates the meter is reporting load level for outlets 1-8; Bank 2 LED indicates the meter is reporting load level for outlets 9-16; Both LEDs lighted indicates the meter is reporting load level for all outlets combined
Switches	Pressing the display toggle switch advances the local display of power consumption for the 3 reported segments: Bank 1, Bank 2 and Banks 1+2 combined
PHYSICAL	
Form Factors Supported	2U rackmount
Material of Construction	Metal
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / cm)	19.81 x 42.67 x 50.55
Shipping Dimensions (hwd / in.)	7.80 x 16.80 x 19.90
Shipping Weight (kg)	7.44
Shipping Weight (lbs.)	16.40
Unit Dimensions (hwd / cm)	8.9 x 44.5 x 31.75
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12.5
Unit Weight (kg)	6.21
Unit Weight (lbs.)	13.7
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems



SPECIAL FEATURES	
High Availability PDU Features	Auto Probe Monitoring (included)
STANDARDS & COMPLIANCE	
Certifications	Tested to UL (USA), CSA (Canada), NOM (Mexico), Class A (emissions), RoHS compliant, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>