


## 1.4kW Single-Phase Monitored PDU with LX Platform Interface, 120V Outlets (16 5-15R), 10 ft. (3.05 m) Cord with 5-15P Plug, 0U, TAA

MODEL NUMBER: PDUMNV15LX



Cost-effective 1.4kW PDU distributes and monitors single-phase power in an IT or industrial environment. Built-in network interface helps you remotely monitor load levels to prevent overloads that cause downtime.

### Description

The PDUMNV15LX 1.4kW Single-Phase Monitored PDU provides real-time remote monitoring of voltage, frequency and load levels via built-in network interface. Recommended for any IT or industrial application, it features 16 NEMA 5-15R outlets with included cord retention brackets to prevent cables from becoming accidentally disconnected. A 10-ft. (3.05 m) cord with NEMA 5-15P plug connects the PDU to a compatible AC power source, generator or protected UPS.

The built-in Java-free HTML5-based LX Platform network interface enables full remote access for PDU status monitoring and email notifications via secure web browser, SNMP, telnet or SSH. It supports 10/100 Mbps auto-sensing for optimum communication with an Ethernet network. Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities. Protocols supported include HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP.

A digital ammeter allows you to monitor the PDU's current level in real time to ensure it remains well below maximum capacity with no danger of overload. The PDU mounts in 0U of space in EIA-standard 19-inch racks using the included toolless mounting buttons or the included rack-mounting brackets. Use the included PDUMVROTATEBRKT kit to install the unit with outlets facing the rear for better airflow or equipment access.

### Features

#### Distributes Network-Grade Single-Phase Power

- 1.4kW 120V monitored PDU with single-phase input/output

### Highlights

- 1.4kW 120V single-phase monitored PDU
- 16 NEMA 5-15R outlets with cord retention brackets
- Pre-installed WEBCARDLX with latest version of PADM20 for enhanced remote management
- Digital ammeter for on-site load monitoring in real time
- NEMA 5-15P input with 10-ft. (3.05 m) AC power cord

### Package Includes

- PDUMNV15LX 1.4kW Single-Phase Monitored PDU
- Built-in LX Platform interface
- Configuration cable
- (16) Cable ties
- (2) Cord retention brackets
- Rack-mounting hardware
- PDUMVROTATEBRKT mounting bracket accessory
- Owner's manual



- NEMA 5-15P with 10-ft. (3.05 m) cord connects to compatible AC power source
- Firmware upgrades support future product enhancements

#### **16 Outlets Distribute AC Power**

- 16 NEMA 5-15R outlets deliver power to connected equipment
- Cord retention brackets help prevent cables from becoming accidentally disconnected

#### **Digital Ammeter**

- Reports total connected equipment load
- Supports IP-address self-ID
- Rotates 180° for easy reading at either angle

#### **Built-In LX Platform Interface**

- Pre-installed WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities
- PADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations
- Allows full remote access for power monitoring with email notifications via secure web browser, SNMP, telnet or SSH
- Supports 10/100 Mbps auto-sensing for communication with an Ethernet network
- Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities
- No Java required

#### **Broad Communications Compatibility**

- Supports HTTP, HTTPS, SMTP, SNMPv1, SNMPv2, SNMPv3, telnet, SSH, FTP, DHCP and NTP
- Supports automatic and manual assignment of IP address

#### **Easy 0U Installation in EIA-Standard 19 in. Racks**

- Mounts vertically using included toolless buttons or rack-mounting brackets
- Included PDUMVROTATEBRKT allows mounting with rear-facing outlets

#### **TAA-Compliant**

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## **Specifications**

| <b>OVERVIEW</b> |              |
|-----------------|--------------|
| UPC Code        | 037332205322 |



|  |   |
|--|---|
| PDU Type                                     | Monitored   |
| <b>INPUT</b>                                 |   |
| PDU Input Voltage                            | 120V  |
| Recommended Electrical Service               | Single-phase 15A 120V service   |
| Maximum Input Amps                           | 12  |
| PDU Plug Type                                | NEMA 5-15P  |
| Input Phase                                  | Single-Phase  |
| Input Cord Length (ft.)                      | 10  |
| Input Cord Length (m)                        | 3.05  |
| <b>OUTPUT</b>                                |   |
| Output Capacity Details                      | 1.44kW (120V) / 12A total capacity; 12A max per outlet  |
| Frequency Compatibility                      | 50 / 60 Hz  |
| Output Receptacles                           | (16) 5-15R  |
| Output Nominal Voltage                       | 120V  |
| Overload Protection                          | n/a   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |   |
| Reported Load Segments                       | Supports local and remote monitoring of PDU output current in amps  |
| Front Panel LCD Display                      | Digital meter reports PDU output current in amps and Scroll IP-address information; Display can be rotated 180 degrees for installation with the input cable at the top                           |
| Front Panel LEDs                             | n/a   |
| Switches                                     | Press the SCROLL IP / ROTATE button and release after one second to display the configured IP address in 2 digit intervals; Press and release after two seconds to rotate the display 180 degrees |
| <b>PHYSICAL</b>                              |   |
| Form Factors Supported                       | 0U vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks   |
| Material of Construction                     | Metal   |
| PDU Form Factor                              | Vertical (0U)   |
| Shipping Dimensions (hwd / cm)               | 12.95 x 16.00 x 133.10  |
| Shipping Dimensions (hwd / in.)              | 5.10 x 6.30 x 52.40   |
| Shipping Weight (kg)                         | 4.13  |
| Shipping Weight (lbs.)                       | 9.10  |
| Unit Dimensions (hwd / cm)                   | 124.5 x 5.6 x 4.45  |
| Unit Dimensions (hwd / in.)                  | 49 x 2.19 x 1.75  |
| Unit Weight (kg)                             | 3.18  |



|                                     |   |
|-------------------------------------|---|
| Unit Weight (lbs.)                  | 7   |
| <b>ENVIRONMENTAL</b>                |   |
| Operating Temperature Range         | 0C ~ 40C (32F ~ 104F)   |
| Storage Temperature Range           | -30°C to +60°C (-22°F to +140°F)  |
| Relative Humidity                   | 5-95% non-condensing  |
| <b>COMMUNICATIONS</b>               |   |
| SNMP Compatibility                  | Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems             |
| <b>SPECIAL FEATURES</b>             |   |
| High Availability PDU Features      | Auto Probe Monitoring (included)  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |   |
| Certifications                      | Tested to UL 60950-1: 2007 (USA), CAN/CSA-C22.2 NO. 60950-1-07 (Canada), FCC Class A Part 15 (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant |
| <b>WARRANTY</b>                     |   |
| Product Warranty Period (Worldwide) | 2-year limited warranty   |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>