

## 2kW Single-Phase Local Metered PDU, 100-127V Outlets (36 5-15/20R), L5-20P/5-20P adapter, 0U Vertical, 72-in.

MODEL NUMBER: PDUMV20-72



### Highlights

- Local Metered single phase 100-127V 16A 0U 72-in. / 183cm vertical rackmount PDU
- Two-digit current meter reports output current in amps
- Attached 15-ft. (4.57 m) cord with NEMA L5-20P plug and 5-20P adapter
- 36 NEMA 5-15/20R outlets
- Toolless button mount and bolt-down bracket installation hardware included

### Package Includes

- PDUMV20-72 Local Metered Vertical PDU
- (1) L5-20P to 5-20P plug adapter
- Mounting hardware and spare mounting buttons
- Instruction manual with warranty information

### Features

- 16A single phase 100-127V Local Metered Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- Attached NEMA L5-20P input plug with 15-ft. (4.57 m) line cord and 5-20P adapter
- 0U 72-in. / 183cm vertical rackmount format installs using no rack spaces
- 36 NEMA 5-15/20R outlets
- Includes 20A circuit breaker and lighted power switch inside a transparent protective cover
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

## Specifications

OVERVIEW	
UPC Code	037332182838
PDU Type	Local Metered
INPUT	
PDU Input Voltage	100; 120; 125; 127
Recommended Electrical Service	Single-phase 20A 100-127V service
Maximum Input Amps	16
Maximum Input Amps Details	Agency de-rated to 16A continuous

PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
<b>OUTPUT</b>	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 16A total capacity; 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(36) 5-15/20R
Output Nominal Voltage	100-127V
Overload Protection	20A circuit breaker
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Digital meter reports PDU output current in amps
Switches	Lighted on/off switch with integrated transparent safety cover
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	No
<b>PHYSICAL</b>	
Material of Construction	Aluminum
Form Factors Supported	Vertical
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	2.40 x 6.65 x 75.79
Shipping Dimensions (hwd / cm)	6.10 x 16.89 x 192.51
Shipping Weight (lbs.)	7.67
Shipping Weight (kg)	3.48
Unit Dimensions (hwd / in.)	72.470 x 1.500 x 1.640
Unit Dimensions (hwd / cm)	184.1 x 4.2 x 3.81
Unit Weight (lbs.)	6.14
Unit Weight (kg)	2.79
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000

Operating Elevation (m)	0-3000
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	RETIE (Colombia); NOM (Mexico); UL 60950-1
Product Compliance	RoHS; FCC Part 15 Class A (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty