

# SmartOnline S3MT-Series 3-Phase 30kVA Input Isolation Transformer, Delta 480V to 208V Wye, TAA

MODEL NUMBER: **S3MT-30K480V**



30kVA/kW transformer provides 480V (Delta) to 208V (Wye) step-down and isolation protection to a 3-phase UPS and its load.

## Features

### Get Complete Step-Down and Isolation Protection and Prevent Power Disruption

Tripp Lite's S3MT-30K480V 30kVA/kW transformer offers line isolation and protection to the connected 3-phase UPS system and its load. It isolates the UPS and connected components from line surges and spikes caused by utility power disruptions that can damage equipment or corrupt data. The step-down input isolation transformer is ideal for 4-wire (3Ph+N+PE) IT loads in government, manufacturing, healthcare and corporate settings with a 480V electrical feed and 208/120V equipment.

### Performs with High Efficiency up to 97.5%

Not only is the S3MT-30K480V very efficient, with up to 97.5 percent efficiency, but it is also very quiet with a noise profile less than 65 dBA. A built-in circuit breaker on the output side helps prevent dangerous power overloads. Two ball-bearing cooling fans help prevent overheating. An overheat-sensing relay and switch combine with a red LED indicator to provide over-temperature warning and overheating protection.

### Small Footprint for Quick Installation in a Compact Space

The compact footprint enables installation of the S3MT-30K480V with minimal space. The rugged stainless steel housing ships ready for immediate installation with a compatible 20–30kVA/kW Tripp Lite S3M-Series 3-phase UPS system.

## Highlights

- Recommended for government, manufacturing, healthcare and corporate settings
- Up to 97.5% efficiency with a quiet acoustic profile less than 65 dBA
- Resettable protection relay/switch and red LED indicator warn against overheating
- Rugged stainless steel housing with compact footprint comes ready for installation
- Compatible with 20–30kVA/kW Tripp Lite S3M-Series 3-phase UPS systems

## Applications

Protect healthcare, manufacturing, corporate and other IT equipment where the upstream power source is 480V and the load requires a 208V 3-phase UPS

## Package Includes

- S3MT-30K480V 3-Phase 30kVA Input Isolation Transformer
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332253149
Efficiency	95.2% @ full load



Nominal Voltage / Frequency	480V 3-PH / 60Hz
VA / Watt Capacity	30000
Transformer Type	Dry type, Input step-down isolation transformer
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	480V 3-PH Delta
UPS Input Connection Type	Hardwire
Input Phase	3-Phase
<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	30000
Output Capacity (kVA)	30
Output Receptacles	Hardwire
<b>PHYSICAL</b>	
Primary Form Factor	Tower
Cooling Method	2 x BALL BEARING, 120MM (288 TOTAL CFM)
Form Factors Supported	Tower
Shipping Dimensions (hwd / in.)	55.60 x 22.20 x 38.20
Shipping Weight (kg)	322.96
Unit Dimensions (hwd / cm)	120 x 44.2 x 85
Unit Dimensions (hwd / in.)	47.2 x 17.4 x 33.5
Unit Weight (kg)	279.87
Unit Weight (lbs.)	617
<b>ENVIRONMENTAL</b>	
Heat Dissipation (BTU/Hr) @ Full Load	4915
<b>INPUT TRANSFORMER</b>	
Input Voltage	480V
Input Voltage Range	(-45%, +25%) for 40% load (-20%, +25%) for 100% load
Input Amp(s)	51 A
AC Input Configuration	Delta
AC Input Frequency	50/60
Frequency Range	40/70Hz
Voltage Selection	NONE
Input Inrush Current	450 A



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

VA Rating	30K
Input Number of Phases	3PH
AC Output Voltage (V)	480 V
AC Output Amps	83 A
Output Number of Phases	3PH + N
AC Output Configuration	WYE
Output Isolation	Yes
Output Breaker Rating	125 A
Connection Type	TERMINAL BLOCK
LED Warning Light Functions	The over-temperature warning LED light will turn ON when the output/secondary of the Input transformer reaches 160°C ±5°C and will turn OFF when the corresponding transformer cools down to 125°C ±5°C
Over Temperature Reset	If the secondary side of the input transformer reaches temperatures of or higher than 160°C ± 5°C, i.e. a range of 155°C to 165°C (311°F to 329°F), an over-temperature protection relay and thermal switch will activate and will open the breaker on secondary side of the transformer. Once the transformer temperature has cooled down to 125°C ± 5°C, i.e. a range of 120°C to 130°C ( 248°F to 266°F) the warning LED light will turn OFF, and you may manually re-activate (close) the output breaker on the transformer to restart normal operation.
Efficiency @ Half Load	97.5%
Efficiency @ Full Load	95.2%
Heat Dissipation (BTU/Hr) @ Full Load	4915
Audible Noise (dBA @ 1m)	65dB max
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Product Warranty Period (U.S. & Canada)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>