

## 1.44kW Single-Phase 120V Basic PDU, 14 NEMA 5-15R Outlets, NEMA 5-15P Input, 15 ft. Cord, 0U Vertical

MODEL NUMBER: PDUV15



Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Recommended for data centers, server rooms and network wiring closets.

### Description

The PDUV15 1.44kW Single-Phase 120V Basic PDU is an excellent no-frills unit for data centers, server rooms and network wiring closets. Perfectly suited for high-density IT environments, the PDUV15 features 14 NEMA 5-15R outlets. The NEMA 5-15P input plug with long 15-foot (4.5 m) cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. A 15A circuit breaker protects connected equipment from dangerous overloads. The 36-inch all-metal housing supports 0U vertical mounting in EIA-standard 19-inch racks using the included hardware and mounting clips or toolless mounting using the included buttons. You can also mount the PDUV15 on a wall or workbench or under a counter with user-supplied hardware.

### Features

#### Reliable Single-Phase Power Distribution

- Versatile no-frills PDU for data centers, server rooms and network wiring closets
- 14 NEMA 5-15R outlets
- NEMA 5-15P input with 15 ft. cord
- 15A circuit breaker protects outlets against overloads

#### Switchless Design

- Prevents accidental shutdowns and costly downtime

### Highlights

- NEMA 5-15P input with 15 ft. (4.5 m) cord
- 14 NEMA 5-15R outlets
- Switchless design prevents accidental shutdown
- 36 in. all-metal housing
- Supports toolless 0U vertical mounting

### Package Includes

- PDUV15 1.44kW Single-Phase 120V Basic PDU
- Mounting brackets
- Owner's manual



### Versatile Installation Options

- 36 in. all-metal housing
- Supports toolless 0U vertical mounting in EIA-standard 19 in. racks
- Also supports 0U mounting using included hardware
- Rear installation buttons can be relocated to the left or right surface for rear, center or forward-facing outlet orientation
- Also mounts on wall, workbench or under a counter with user-supplied hardware

## Specifications

OVERVIEW	
UPC Code	037332144515
PDU Type	Basic
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per 5-15R outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Switches	n/a
PHYSICAL	
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
Material of Construction	Metal



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / cm)	9.14 x 6.60 x 102.87
Shipping Dimensions (hwd / in.)	3.60 x 2.60 x 40.50
Shipping Weight (kg)	1.77
Shipping Weight (lbs.)	3.90
Unit Dimensions (hwd / cm)	92.63 x 3.81 x 4.17
Unit Dimensions (hwd / in.)	36.47 x 1.5 x 1.64
Unit Weight (kg)	1.64
Unit Weight (lbs.)	3.61
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL 60950-1: 2007 R10.14 (USA) and CAN/CSA-C22.2 No. 60950-1-07+A1:2011+A2:2014 (Canada), NOM (Mexico), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>