


1.4kW 120V Single-Phase Basic PDU - 16 NEMA 5-15R Outlets, 5-15P Input, 15 ft. Cord, 48 in. 0U Rack

MODEL NUMBER: PDUV15-48



Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a data center or network closet.

Features

Single-Phase 120V PDU Distributes Network-Grade Power to Multiple Loads

This basic PDU is an ideal no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Recommended for small to mid-sized data centers, computer rooms and network closets, the PDUV15-48 features 16 NEMA 5-15R outlets for connecting equipment. A 15-foot cord with 5-15P input plug connects to your facility's AC power source, generator or protected UPS system to distribute power to connected loads.

Up-to-Date Safety Features Protect Your Vital Equipment

A lighted on/off switch is protected by a transparent plastic cover to help prevent an accidental shutdown that could lead to costly downtime. A 15A circuit breaker protects connected components from dangerous overloads.

Versatile Installation Options Give You Plenty of Choices

The 48-inch 0U PDU mounts vertically in an EIA-standard 19-inch rack using the included toolless mounting buttons or the included mounting clips and hardware. You may also use the clips to secure the PDU to a wall, counter or other flat, secure surface.

Highlights

- Ideal no-frills PDU for telecom, security, audio/video and other network applications
- 16 NEMA 5-15R outlets distribute AC power to connected equipment
- Lighted power switch with protective cover helps prevent accidental shutdowns
- 15 ft. power cord with NEMA 5-15P input connects to compatible AC source
- 48 in. 0U PDU with included mounting hardware installs in rack or under counter

Applications

Deliver network-grade power to high-density equipment in networking, telecom, security, audio/video and sound reinforcement applications

Package Includes

- PDUV15-48 1.44kW 120V Single-Phase Basic PDU
- Rack-mounting hardware
- Owner's manual

Specifications

| OVERVIEW | |
|--------------------------------|-------------------------------|
| UPC Code | 037332255815 |
| PDU Type | Basic |
| INPUT | |
| PDU Input Voltage | 120V |
| Recommended Electrical Service | Single-phase 15A 120V service |



| | |
|--|--|
| Maximum Input Amps | 12 |
| Maximum Input Amps Details | Agency de-rated to 12A continuous |
| PDU Plug Type | NEMA 5-15P |
| Input Phase | Single-Phase |
| Input Cord Length (ft.) | 15 |
| Input Cord Length (m) | 4.57 |
| OUTPUT | |
| Output Capacity Details | 1.44kW (120V) / 12A total capacity; 12A max per outlet |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (16) 5-15R |
| Output Nominal Voltage | 120V |
| Overload Protection | 15A circuit breaker |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Lighted on/off switch with transparent switch cover |
| PHYSICAL | |
| Form Factors Supported | Vertical (0U) mounting in rack enclosures |
| Material of Construction | Metal |
| PDU Form Factor | Vertical (0U) |
| Shipping Dimensions (hwd / in.) | 51.77 x 3.43 x 2.40 |
| Shipping Weight (kg) | 2.01 |
| Unit Dimensions (hwd / cm) | 123.1 x 3.81 x 4.2 |
| Unit Dimensions (hwd / in.) | 48.47 x 1.5 x 1.64 |
| Unit Weight (kg) | 1.70 |
| Unit Weight (lbs.) | 3.74 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0C ~ 40C (32F ~ 104F) |
| Storage Temperature Range | -30°C to +50°C (-22°F to +122°F) |
| Relative Humidity | 5-95% Non-condensing |
| STANDARDS & COMPLIANCE | |
| Certifications | Tested to UL 60950-1: 2007 R10.14 (USA), CAN/CSA-C22.2 No. 60950-1-07+A1:2011+A2:2014 (Canada), RoHS Compliant |
| WARRANTY | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|-------------------------|
| Product Warranty Period (Worldwide) | 2-year limited warranty |
|--|-------------------------|

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>