


## 12-Outlet (10-15A & 2-20A) Vertical Power Strip, 120V, 20A, 15-ft. Cord, 5-20P, 36 in.

MODEL NUMBER: PS361220



Add extra power outlets in rack-mount, workbench, office, retail displays and telecom applications, or any area that needs to power many electrical devices in close proximity to one another from a single AC wall outlet.

### Description

Need to power many pieces of equipment in close proximity to one another but don't have enough outlets to power them all? Tripp Lite's PS361220 12-outlet vertical power strip will give you the outlets where you need them, when you need them. The PS361220 contains a 15-ft. (14/3 SJT) cord, 10 standard NEMA 5-15R and 2 commercial-use NEMA 5-20R outlets. Each outlet is spaced 2.64-in. apart (center-to-center) – wide enough for many types of transformers or AC adapters without blocking adjacent outlets. Encased in a rugged, all-metal housing, it comes with mounting clips for either vertical and horizontal mounting, making the PS361220 ideal for a variety of uses in rack-mount, workbench, industrial, office and telecom environments. An illuminated, rocker-style, power switch with a transparent guard prevents accidental turn-offs, while a 20-amp circuit breaker guards against dangerous circuit overloads. To match the decor of most professional settings, it has an extruded aluminum housing with black receptacles.

### Features

#### Multi-Outlet 120V Power Distribution for Rack-Mount, Raceway and Workbench Applications

- 1800W, 120V, 20A, corded, multi-outlet power strip that safely connects multiple electrical devices to a single AC wall socket
- Saves the time and cost of installing new power outlets in un-powered areas
- Ideal for branch circuit power distribution to telecommunications, computers or internetworking equipment in rack enclosures, workbenches, table tops, work stations, offices, factories, repair shops, hobby shops, test stands and engineering labs

#### 12 Convenient Outlets Power All Standard Electrical Equipment

### Highlights

- 12-outlet (ten 5-15R & two 5-20R) power strip with a 15-ft. Cord and an industrial-grade 5-20P plug
- Rated at 1800W, 120V, featuring a 20A resettable circuit breaker to prevent circuit overloads
- Easy-to-install, vertical or horizontal mounting with included mounting clips
- Rocker-style, illuminated power switch with safety cover to prevent accidental turn offs
- RoHS-compliant and certified to meet UL 1363 standards

### Package Includes

- PS361220
- Mounting hardware
- Instruction manual



- Features 12 outlets (10 NEMA 5-15R and 2 NEMA 5-20R) that are compatible with all standard electrical and electronic equipment
- Each outlet is 2.64 inches apart (center to center) - wide enough to fit transformers or AC adapters without blocking adjacent outlets, so you can fully utilize the power strip all the time
- An extra-long, 15-ft., 14 AWG, 3-wire, SJT cord can reach wall outlets mounted in a different area or room from where it draws AC power, putting you in control of getting reliable power where you need it most

#### **Easy-to-Install, Vertical and Horizontal Mounting Options**

- Offers a convenient method of optional horizontal or vertical power distribution. Mounting clips are included.
- Its 36-in. length and strip-style, bench/cabinet, form factor fits in the most confined spaces unobtrusively
- Weighing less than 4 lbs., the PS361220 is both easy to handle and effortless to install

#### **Built-In, Automatic Safety Features**

- An illuminated, rocker-style, power switch with a transparent guard prevents accidental turn offs, while still allowing you to see whether the PS361220 is operational at a glance
- An integral, 20-amp resettable circuit breaker prevents dangerous circuit overloads that can irreversibly damage connected equipment
- The breaker automatically disconnects AC input power to the PS361220 when it detects that the equipment load is drawing too much current

#### **Rugged, Durable Housing**

- A rugged, all-metal housing is durably constructed to stand up to demanding network, laboratory or factory environments
- An attractive, extruded aluminum housing with stylish black receptacles matches the decor of most professional settings

## **Specifications**

<b>OVERVIEW</b>	
UPC Code	037332186638
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120



Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R; (2) 5-20R
Circuit Breaker (amps)	20
Transformer Accommodation	(6) Yes
Right-Angle Outlets	No
Outlet Spacing	2.64 in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Antimicrobial Coating	No
Color	Silver
Color (AC Line Cord)	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Included Mounting Accessories	Includes mounting clips
Integrated Keyhole Mounting Slots	No
Material of Construction	Aluminum
Outlets Measurement (Center to Center)	2.64"
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	6.10 x 11.18 x 101.60
Shipping Dimensions (hwd / in.)	2.40 x 4.40 x 40.00
Shipping Weight (kg)	2.04
Shipping Weight (lbs.)	4.50
Unit Dimensions (hwd / cm)	3.18 x 3.81 x 91.4
Unit Dimensions (hwd / in.)	36 x 1.5 x 1.25
Unit Weight (kg)	1.72
Unit Weight (lbs.)	3.79



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>STANDARDS &amp; COMPLIANCE</b>	
Canada	cUL
UL1363 (Power Tap)	UL1363
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>