

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

For Patient-Care Vicinity - UL 1363A Medical-Grade Power Strip, 4 Hospital-Grade Outlets, 10 ft. (3.05 m) Cord, Drip Shield

MODEL NUMBER: PS410HGOEMX



Power strip with built-in cord manager and optional drip shield supplies power to movable plug-connected components mounted to IV poles, carts and mobile medical workstations inside or outside of patient-care vicinities.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted 120V, 50/60 Hz power strip complies with UL 1363A specifications

Exclusive Antimicrobial Protection Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power Integrated cord wrap provides easy cord management Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Dual, resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shut-off Drip shield adds extra measure of safety against liquids and moisture

Ready to Use Right Out of the Box Built-in mounting tabs and flanges make the PS410HGOEMX easy to install on a variety of surfaces

Specifications

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A specifications
- 10-ft. (3.05 m) cord with NEMA 5-15P-HG hospital-grade plug
- Optional drip shield provides extra protection from liquids

Package Includes

- PS410HGOEMX UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets, 10 ft. Cord, Cord Wrap and Drip Shield
- Owner's Manual with maintenance requirements

OVERVIEW	
UPC Code	037332168948
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes
Cable Management	Bar
Receptacle Color	White

Shipping Dimensions (hwd / in.)	10.12 x 6.10 x 2.36
Shipping Dimensions (hwd / cm)	25.70 x 15.49 x 5.99
Shipping Weight (lbs.)	3.06
Shipping Weight (kg)	1.39
Unit Dimensions (hwd / in.)	9.940 x 4.280 x 2.170
Unit Dimensions (hwd / cm)	25.25 x 10.8712 x 5.51
Unit Weight (lbs.)	2.84
Unit Weight (kg)	1.29
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Antimicrobial	Yes
Built-in Cable Management	Yes
Built-In Circuit Breaker	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty