

SmartPro LCD 120V 1500VA 900W Line-Interactive UPS, AVR, Extended Runtime, 2U Rack/Tower, LCD, USB, DB9, 8 Outlets

MODEL NUMBER: **SMART1500LCDXL**



Provides reliable 1500VA/900W power protection with expandable runtime for your desktop computer, network workstation, audio/video components or media center. Protects against surges, line noise, blackouts and brownouts.

Description

The SMART1500LCDXL SmartPro LCD 120V, 1500VA/900W Line-Interactive Uninterruptible Power Supply provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up your desktop computer or audio/visual components, this line-interactive UPS switches to battery backup mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Eight NEMA 5-15R outlets protect against surges, as well as provide up to 12 minutes of UPS battery support at half-load (450W) and 4 minutes of support at full load (900W). You can get even more runtime by connecting an optional BP24V15RT2U external battery pack.

Automatic voltage regulation (AVR) corrects severe undervoltages as low as 75V and overvoltages as high as 147V without using any battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 1038-joule surge suppression rating protects your equipment from harmful power surges.

Space-saving NEMA 5-15P right-angle plug with 6-foot cord connects to any NEMA 5-15R socket. Large rotatable LCD screen shows real-time input voltage, load, AVR, remaining battery runtime and battery statuses at a glance. With Tripp Lite's PowerAlert software (available via free download), the SMART1500LCDXL enables safe unattended system shutdown and file saves in case of a prolonged power failure.

Features

Reliable Battery Backup Provides 1500VA/900W high-performance power protection for desktop computers, audio/video components, media centers and other electronics Supports 50% load (450W) up to 12 minutes and full load (900W) up to 4 minutes 97% full-load efficiency rating saves money in energy costs Audible alarm indicates loss of utility power, low battery and overload conditions Optional BP24V15RT2U external battery pack easily connects for expanded runtime
Optimized Outlets 8 NEMA 5-15R outlets provide battery backup and protect against surges or spikes that can harm equipment or data

Highlights

- Supports a half-load (450W) up to 12 min. during power outage
- Supports a full load (900W) up to 4 min. during power outage
- Features 8 protected NEMA 5-15R outlets
- Offers automatic voltage regulation (AVR)
- Extends runtime with optional BP24V15RT2U external battery pack

Package Includes

- SMART1500LCDXL SmartPro LCD 120V 1500VA/900W Line-Interactive UPS
- USB cable
- DB9 serial cable
- Telephone cable
- Mounting hardware
- Owner's Manual



Automatic Voltage Regulation (AVR)Corrects undervoltages as low as 75V and overvoltages as high as 147V without drawing battery backup power

Rotatable LCD Status ScreenLarge LCD screen shows real-time input voltage, load, AVR and battery statusesAutomatically displays remaining battery runtime in minutes during power outageRotates for easy viewing in both horizontal and vertical installationsBrightness control offers bright and dim selection options

AC Line, Tel/DSL and Ethernet Surge SuppressionSurge suppression rating of 1038 joules protects connected equipment and data from harmful power surgesBuilt-in RJ-45 jacks protect single-line tel/DSL or network Ethernet connection

EMI/RFI Line Noise FilteringRemoves electromagnetic and radio frequency interference that can disrupt or damage your equipment's performance

USB and DB9 Communication Ports and Free PowerAlert SoftwareHID-compliant USB port integrates with built-in power management and auto-shutdown of Windows and Mac OS XUSB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert

Flexible Installation OptionsSpace-saving NEMA 5-15P right-angle plug with 6-foot cord connects to any NEMA 5-15R socketAdapts to vertical or horizontal installation without special hardwareIncludes 2U brackets for rack-mount installation

Specifications

OVERVIEW	
UPC Code	037332159885
OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA Capacity (kVA)	1.50
Output Watt Capacity (Watts)	900
Output kW Capacity (kW)	0.90
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(8) 5-15R
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Individually Controllable Load Banks	No
INPUT	
Rated input current (Maximum Load)	8.6A
Nominal Input Voltage(s) Supported	110V AC; 115V AC; 120V AC



UPS Input Connection Type	5-15P; Right-Angled
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	4 min. (900w)
Half Load Runtime (min.)	12 min. (450w)
Expandable Battery Runtime	Extended runtime supported via optional external battery pack (limit 1)
External Battery Pack Compatibility	BP24V15RT2U (limit 1)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	See RBC Selector for replacement battery information
Battery Access	Battery access door enables hot-swappable, user replaceable internal battery
Expandable Runtime	Yes
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	LCD interface reports Input Voltage, Output Voltage, Battery Charge Percentage, Estimated Runtime in Minutes, Load Percentage, Load Watts; Additional LCD icons report battery charge level (5 "bars"), Line Power Mode, Battery Mode, Replace Battery and Auto-Voltage Regulation / AVR status; LCD interface control options include Alarm Disable, Display Scrolling, Initiate Self-test, LCD brightness, External Battery setting and line sensitivity
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions; Alarm can be permanently silenced via LCD interface
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	1038
UPS AC Suppression Response Time	Instantaneous



UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	2 post 19 inch rackmount; 4 post 19 inch rackmount; Tower
Included Mounting Accessory Description	Included mounting brackets enable installation in 2 and 4 post racks, plus upright tower configurations; Set of 4 rubber-feet enable no-slip horizontal desktop placement installation
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.3 x 10.5
UPS Power Module Dimensions (hwd, cm)	8.89 x 43.94 x 26.67
Rack Height	2U
Minimum Required Rack Depth without External Battery Pack (in.)	13.5
Minimum Required Rack Depth with External Battery Pack (in.)	13.5
UPS Power Module Weight (lbs.)	29.4
UPS Power Module Weight (kg)	13.34
Shipping Dimensions (hwd / in.)	7.40 x 15.00 x 21.20
Shipping Dimensions (hwd / cm)	18.80 x 38.10 x 53.85
Shipping Weight (lbs.)	33.20
Shipping Weight (kg)	15.06
Cooling Method	Fan
UPS Housing Material	Polycarbonate
Primary UPS Height (mm)	89
Primary UPS Width (mm)	439
Primary UPS Depth (mm)	267
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	Up to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	78
Battery Mode BTU / Hr. (Full Load)	721
AC Mode Efficiency Rating (100% Load)	97%
COMMUNICATIONS	



Communications Interface	USB (HID enabled); DB9 Serial; Contact closure
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; DB9 port also supports contact-closure messaging for power-fail (pins 1 & 9) and power-restored (pins 1, 8)
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB and DB9 Serial cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds AC to battery mode / 3 milliseconds battery to AC mode
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>