

## Safe-IT UL 2930 Medical-Grade Power Strip for Patient Care Vicinity, 6 Hospital-Grade Outlets, Safety Covers, Antimicrobial, 6 ft. Cord, Dual Ground

MODEL NUMBER: PS-606-HGDG



Delivers power to movable plug-connected equipment attached to IV poles, crash carts and other mobile medical devices in patient care vicinities.

### Features

#### UL 2930 Medical-Grade Power Strip Approved for Patient Care Vicinities

The PS-606-HGDG features six NEMA 5-15R-HG "green dot" hospital-grade outlets that supply power to medical equipment used inside patient care vicinities, including operating rooms, therapy rooms and imaging environments. It meets UL 2930 standards with a NEMA 5-15P-HG plug that provides redundant ground connection. The innovative input plug eliminates the need for an additional ground wire, which reduces cable clutter, the potential shock risk and risk of tripping to a patient in the event of a ground fault.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ power strip is protected by an antimicrobial coating that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

#### Premium Safety Features Help Ensure Proper Power Connections

With no central power switch, this power strip presents no danger of accidental shutoff and cutting off power to essential devices. Resettable 15-amp circuit breakers protect connected equipment against overloads. Locking plastic safety covers are included to block access to unused outlets.

#### Ready for Installation in Demanding Medical Environments

The six-foot cord allows positioning the medical device away from a standard NEMA 5-15R duplex wall outlet. Built-in mounting flanges and integrated keyhole slots let you mount the all-metal housing to benches, stands, mobile carts, IV poles or any other areas containing multiple cord-and-plug-connected medical electrical equipment used in patient care vicinities.

### Highlights

- Medical-grade power strip approved for use inside and outside patient care vicinities
- Meets UL 2930 and NFPA 99 standards for enhancing patient, staff and visitor safety
- Input plug with dual ground connection
- 6 ft. power cord allows some flexibility in placing power strip away from wall outlet
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew
- Patent Pending

### Package Includes

- PS-606-HGDG UL 2930 Medical-Grade Power Strip, 6 Outlets, 6 ft. Cord
- (6) Outlet safety covers
- Owner's manual

## Specifications

### OVERVIEW



UPC Code	037332262264
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	10 gauge; 12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Plug Type Details	Redundant (double) ground connection
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Included Mounting Accessories	Mounting tabs and flanges
Mounting Holes or Slots	Yes



Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	Inner outlets = 32.5mm
Receptacle Color	White
Shipping Dimensions (hwd / in.)	3.43 x 10.43 x 17.60
Shipping Dimensions (hwd / cm)	8.71 x 26.49 x 44.70
Shipping Weight (lbs.)	4.30
Shipping Weight (kg)	1.95
Unit Dimensions (hwd / in.)	1.860 x 2.500 x 13.630
Unit Dimensions (hwd / cm)	21.97 x 6.35 x 3.81
Unit Weight (lbs.)	2.25
Unit Weight (kg)	1.02
Mounting Details	Includes flanges
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	Yes
Rotatable Outlets	No
Built-in Cable Management	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 2930
Product Compliance	NFPA 99: 10.2.3.6; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>