


# 6-Outlet Power Strip - British BS1363A Outlets, Individually Switched, 220-250V, 13A, 3 m Cord, White

MODEL NUMBER: **PS6B35W**



Eco-friendly 6-outlet power strip with individually controlled outlets distributes electricity to home and office electronics.

## Features

**46.5 cm Power Strip Delivers Electricity to 6 Devices at the Same Time** Compatible with standard electrical equipment, this Protect It!® power strip features six BS1363A outlets and a durable white plastic housing. It is ideal for powering almost anything with a compatible plug, including computers and mobile devices to appliances and power tools.

**Individual On/Off Switches Save Energy and Money** All six outlets have individual on/off switches, so if you aren't using the device plugged into it, you can power off the outlet to save energy and lower your electric bill.

**Designed to Give You Flexibility in Placing the Power Strip Where It's Most Needed** The power strip features a space-saving right-angle BS1363A plug that helps you connect to a wall outlet located behind furniture that is placed flush against the wall. The plug is attached to a 3-meter power cord, which gives you more choices in placing the power strip away from the connected AC outlet.

**Vertical or Horizontal Mounting for Desks and Workbenches** Keyhole-shaped mounting slots on the back of the power strip allow you to permanently install it on any flat surface, including walls, with user-supplied hardware.

**Premium Circuit Breaker Designed for Protecting Your Valuable Equipment** An integrated 13A circuit breaker protects all outlets and automatically cuts power if the protection circuit is incapacitated, preventing equipment damage.

## Highlights

- 6 BS1363A outlets distribute power to appliances, tools, lighting and other electronics
- Individually switched outlets let you conserve energy by turning off outlets not in use
- 3 m cord with BS1363A plug offers flexible placement in relation to an AC wall outlet
- Rear keyhole slots enable mounting to desk or workbench for easy access to outlets
- 13A circuit breaker shuts down all UK outlets for safety in case of overload

## Applications

- Distribute power to computer equipment and other devices in an office, workbench, retail or telecom environment
- Mount a power strip to the edge of a desk or workbench for easy access to outlets
- Turn off outlets not currently in use to save energy costs

## Package Includes

- PS6B35W 6-Outlet Power Strip, British BS1363A Outlets, Individually Switched, White

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332251596 |

| <b>INPUT</b>                                 |  |
|--|--|
| Nominal Input Voltage(s) Supported           | 230V AC  |
| Recommended Electrical Service               | 230V (220-250V)  |
| Voltage Compatibility (VAC)                  | 220-250  |
| Input Plug Type                              | British  |
| Input Cord Length (ft.)                      | 9.8  |
| Right-Angle Plug                             | Yes  |
| Input Cord Length (m)                        | 2.99   |
| Integrated Cord Clip                         | No   |
| <b>OUTPUT</b>                                |  |
| Frequency Compatibility                      | 50 / 60 Hz   |
| Output Receptacles                           | (6) British BS 1363A   |
| Circuit Breaker (amps)                       | 13   |
| Overload Protection                          | Combo power switch and circuit breaker   |
| Outlet Orientation                           | Right-angled   |
| Right-Angle Outlets                          | Yes  |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Diagnostic LED(s)                            | Yes  |
| Switches                                     | Two position power switch  |
| <b>SURGE / NOISE SUPPRESSION</b>             |  |
| Protection Modes                             | Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression |
| Automatic Shut-Off                           | No   |
| <b>DATALINE SURGE SUPPRESSION</b>            |  |
| Cable (Coax) Protection                      | No   |
| Network (Ethernet) Protection                | No   |
| Telephone/DSL Protection                     | No   |
| <b>PHYSICAL</b>                              |  |
| Color  | White  |
| Material of Construction                     | Plastic  |
| Power Cord Color                             | White  |
| Housing Color                                | White  |
| Mounting Holes or Slots                      | Yes  |



Powering Business Worldwide



|                                      |                                |
|--------------------------------------|--------------------------------|
| Receptacle Color                     | White                          |
| Shipping Dimensions (hwd / in.)      | 18.30 x 3.90 x 3.40            |
| Shipping Dimensions (hwd / cm)       | 46.48 x 9.91 x 8.64            |
| Shipping Weight (lbs.)               | 1.90                           |
| Shipping Weight (kg)                 | 0.86                           |
| Unit Dimensions (hwd / in.)          | 18.300 x 3.400 x 3.000         |
| Unit Dimensions (hwd / cm)           | 11.6 x 2.9 x 2.9               |
| Unit Weight (lbs.)                   | 0.81                           |
| Unit Weight (kg)                     | 0.37                           |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                |
| Rotatable Outlets                    | No                             |
| Antimicrobial                        | No                             |
| Built-In Circuit Breaker             | Yes                            |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                |
| Product Compliance                   | RoHS; CE (Europe); REACH; UKCA |
| <b>WARRANTY &amp; SUPPORT</b>        |                                |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty      |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.