

## SmartOnline S3MX Series 3-Phase 380/400/415V 160kVA 144kW On-Line Double-Conversion UPS

MODEL NUMBER: **S3M160KX**



Highly efficient 94% on-line UPS with compact design protects mission-critical equipment against downtime due to power disturbances.

### Features

**Battery Backup and VFI Operation Protect Critical Loads**The SmartOnline® S3M160KX IGBT UPS supports the continuous availability of your most important loads through all power conditions, providing a compact backup power platform that's easy to manage and inexpensive to operate. Sophisticated voltage and frequency independent (VFI) operation and advanced IGBT rectifier technology with DSP control deliver reliable output power quality. Providing up to 160kVA of clean, continuous power, this 3-phase UPS system is perfect for critical applications in IT, communications, corporate, commercial, retail, financial, security, transportation, emergency and light industrial environments.

**Best-in-Class Footprint for Easy Integration into Your Network Application**This on-line double-conversion UPS system has a very small footprint of just 0.56 square meters. It requires less valuable space in your data center, and you can install the UPS system in spaces that would previously have required expensive retrofitting.

**Efficient Operation and Design Reduces Cost of Ownership**This IGBT UPS benefits from highly efficient transformer-free double-conversion technology that delivers operating cost savings. It achieves 94% efficiency in double-conversion mode and up to 98% in ECO mode, reducing your power and cooling costs. A low THDi (<3%) improves generator compatibility. A low THDv (2%) and active power factor correction improve output performance. The hardware and firmware platform design reduces the number of unique boards, improving mean time to repair (MTTR) and resulting in reduced downtime. Built-in static and maintenance bypass transfer UPS load to utility power during faults, overloads and maintenance, which also avoids costly system downtime.

**External Batteries Supply Reliable Backup with Expandable Runtime Options**The S3M160KX uses external scalable battery cabinets, such as BP480V65 and BP480V100 (sold separately), to provide up to three hours of backup support in case of a power failure. Add the optional TEMPC100200 thermostat kit to enable temperature-compensated charging for optimized battery lifespan. The UPS system automatically restarts after a lengthy power outage.

**Intuitive Color Touchscreen Display Delivers Important Performance Information at a Glance**The large (25.4 cm/10 inches) front-panel color interface enables comprehensive local monitoring and control capability. It displays critical operating conditions and diagnostic data, such as phase load levels, available runtime, alarm status, battery charge, and voltage and frequency values. Six LEDs indicate bypass, on-line, inverter, battery and alarm/fault modes.

**Network Management Card Offers Remote Monitoring and Control**The optional Java-free WEBCARDLX network management card (sold separately) enables remote management through embedded HTML5 web, SSH/telnet and SNMP interfaces, as well as integration with a wide range of network management systems and DCIM platforms. A Remote Emergency Power Off (REPO) port allows shutdown from a safe distance during emergencies.

**Parallel Capability Provides Additional Capacity**Connect two S3M160KX units in parallel using

### Highlights

- Best-in-class footprint and power density minimize space requirements for up to 160kVA
- Large (25.4 cm/10 in.) color touchscreen display enables user-friendly local management
- High efficiency (94% on-line, 98% ECO mode) helps reduce operating costs
- Optional WEBCARDLX network management card allows cost-effective remote management
- Parallel capability provides increased capacity and fault tolerance

### Applications

- Fit 160kVA UPS in best-in-class footprint to save space for revenue-generating equipment
- Back up critical IT equipment and data in network, telecom, financial and light industrial applications
- Maintain data-center operations during all power conditions

### Package Includes

- S3M160KX SmartOnline S3MX Series 3-Phase 380/400/415V 160kVA 144kW On-Line Double-Conversion UPS
- P100200KIT parallel cable kit
- RS-232 cable
- Owner's manual



separate/shared battery cabinets for increased capacity and fault tolerance (N+1 redundancy).

## Specifications

OVERVIEW	
UPC Code	037332225443
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	275A
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire plus ground (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Circuit Breakers	400A (3 pole)
Input Phase	3-Phase
Power Factor (Input)	.99PF (100% load)
THDi	<3% (100% load)
OUTPUT	
Output Volt Amp Capacity (VA)	160000
Output kVA Capacity (kVA)	160.00
Output Watt Capacity (Watts)	144000
Output kW Capacity (kW)	144.00
Output Capacity Details	Supports up to 100% load continuously in double conversion mode; Supports up to 110% load for 60 minutes, up to 125% load for 10 minutes, up to 150% load for 1min and greater than 150% for 1 milliseconds before switching to bypass mode; Inverter mode is automatically restored as load levels are reduced to less than 100%; Configuration options support up to 2 S3M160KX systems wired in parallel for increased capacity, or redundancy (N+1) to increase fault-tolerant and redundant operation
Power Factor	0,9
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+/- 1%
Output Voltage Regulation (Economy Line Mode)	+/-15V of nominal
Output Voltage Regulation (Battery Mode)	+/- 1%
Output AC Waveform (AC Mode)	Pure Sine wave





Shipping Dimensions (hwd / in.)	63.40 x 27.80 x 44.30
Shipping Weight (kg)	335.52
Shipping Weight (lbs.)	739.70
UPS Housing Material	Steel
UPS Power Module Dimensions (Height x Width x Depth, mm)	1455 x 567 x 995
UPS Power Module Dimensions (hwd, cm)	145.54 x 56.69 x 99.57
UPS Power Module Dimensions (hwd, in.)	57.3 x 22.32 x 39.20
UPS Power Module Weight (kg)	308.99
UPS Power Module Weight (lbs.)	681.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C to +40C (32-104F)
Storage Temperature Range	-15C to 60C (5 to +140F) without battery
Relative Humidity	5 to 95%, non-condensing
Operating Elevation (ft.)	< 3280ft (Capacity de-rates by 1% for every 328ft over 3280ft )
Audible Noise	<73dBA at 1meter
Operating Elevation (m)	< 1000m (Capacity de-rates by 1% for every 100m over 1000m)
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card-WEBCARDLX">WEBCARDLX</a>&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Programmable-RS-485-Management-Accessory-Card-for-Select-3-Phase-UPS-Systems-MODBUSCARDSV">MODBUSCARDSV</a>&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Programmable-Relay-I-O-Card-Tripp-Lite-SVIX-SVX-SV-UPS-Systems-RELAYCARDSV">RELAYCARDSV</a>&nbsp;&nbsp;&nbsp;
Network Monitoring Port Description	Card accessory slot supports network management interface WEBCARDLX card or a programmable I/O RELAYCARDSV relay card options
Communications Cable	DB9/RS-232 cable included
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	Zero transfer time Online to Battery, Inverter to Bypass 0ms (Synchronous), and Inverter to ECO mode < 20ms.
Low Voltage Transfer to Battery Power (Setpoint)	120V(Ph-N), 208V (Ph-Ph) @ 50% load / 176V (Ph-N), 305V (Ph-Ph) @ 100% load.
High Voltage Transfer to Battery Power (Setpoint)	276 (Ph-N), 478V (Ph-Ph) @ 50% or 100% load.
<b>SPECIAL FEATURES</b>	
Grounding Lug	Yes



Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Manual bypass switch; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	CE
Certification Details	IEC 62040-1:2008+A1 (Safety); EN 62040-2:2006 (Category C3)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	<a href="#">Tripp Lite 3-Phase UPS Factory Warranty</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>