

This UPS system has no internal batteries. For a similar UPS system with internal batteries, please see Tripp Lite's S3M30KX.

## SmartOnline S3MX Series 3-Phase 380/400/415V 30kVA 27kW On-Line Double-Conversion UPS, Parallel for Capacity and Redundancy, Single & Dual AC Input, No Internal Batteries

MODEL NUMBER: **S3M30KXD-NIB**



Highly efficient 94% on-line UPS with compact design protects mission-critical equipment against downtime due to power disturbances.

### Features

**Battery Backup Option and VFI Operation Protect Critical Loads**The SmartOnline® S3M30KXD-NIB IGBT UPS supports the continuous availability of your most important loads through all power conditions, providing a compact backup power platform that's easy to manage and inexpensive to operate. Sophisticated voltage and frequency independent (VFI) operation and advanced IGBT rectifier technology with DSP control deliver reliable output power quality. Providing up to 30kVA of clean, continuous power, this 3-phase UPS system is perfect for critical applications in IT, communications, corporate, commercial, retail, financial, security, transportation, emergency and edge infrastructure environments.

**Best-in-Class Footprint for Easy Integration into Your Network Application**This on-line double-conversion UPS system has a very small footprint of just 0.24 square meters. It requires less valuable space in your facility, and you can install the UPS system in spaces that would previously have required expensive retrofitting.

**Efficient Operation and Design Reduces Cost of Ownership**This UPS benefits from highly efficient transformer-free double-conversion technology that delivers operating cost savings. It achieves 94% efficiency in double-conversion mode and up to 98% in ECO mode, reducing your power and cooling costs. A low THDi (<3%) improves generator compatibility. A low THDv (2%) and active power factor correction improve output performance. The hardware and firmware platform design reduces the number of unique boards, improving mean time to repair (MTTR) and resulting in reduced downtime. Built-in static and maintenance bypass transfer UPS load to utility power during faults, overloads and maintenance, which also avoids costly system downtime.

**External Batteries Supply Reliable Backup with Expandable Runtime Options**The S3M30KXD-NIB online double-conversion UPS uses external scalable battery cabinets (sold separately) to provide backup support in case of a power failure. For instance, the Tripp Lite BP480V65 provides up to 41 minutes of extended runtime at full load, and the BP480V40 provides up to 22 minutes. The UPS system automatically restarts after a lengthy power outage.

**Intuitive LCD Interface Delivers Important Performance Information at a Glance**The interactive front-panel LCD interface displays critical operating conditions and diagnostic data, including operating mode, input/output voltage, load, battery voltage, backup runtime and fault conditions. Four LEDs provide information about line, bypass, battery and fault status.

**Network Management Card Offers Remote Monitoring and Control**The optional Java-free

### Highlights

- Best-in-class footprint and power density minimize space requirements for up to 30kVA
- Intuitive LCD interface offers key performance, configuration and diagnostics info
- High efficiency (94% on-line, 98% ECO mode) helps reduce operating costs
- Optional WEBCARDLX network management card allows cost-effective remote management
- Parallel for capacity and redundancy up to 3 units
- Single and dual AC input capability

### Applications

- Fit 30kVA UPS in best-in-class footprint to save space for revenue-generating equipment
- Back up critical IT equipment and data in network, telecom, financial and commercial applications
- Maintain server-room operations during all power conditions, including short blackouts

### Package Includes

- S3M30KXD-NIB SmartOnline S3MX Series 3-Phase 380/400/415V 30kVA 27kW On-Line Double-Conversion UPS (No Internal Batteries)
- RS-232 cable
- Paralleling cable kit
- Owner's manual



WEBCARDLX network management card (sold separately) enables remote management through embedded HTML5 web, SSH/telnet and SNMP interfaces, as well as integration with a wide range of network management systems and DCIM platforms. A Remote Emergency Power Off (REPO) port allows shutdown from a safe distance during emergencies.

**Parallel Capability Provides Additional Capacity** Connect up to three S3M30KXD-NIB units in parallel using separate/shared battery cabinets for increased capacity.

**2-Year Warranty Provides Peace of Mind** The S3M30KXD-NIB is backed by a 2-year limited warranty, ensuring reliability and performance.

## Specifications

OVERVIEW	
UPC Code	037332239747
UPS Type	On-Line
INPUT	
Rated input current (Maximum Load)	46.6A
Nominal Input Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Nominal Input Voltage Description	3-Phase Wye, 4 wire plus ground (L1, L2, L3, N, G)
UPS Input Connection Type	Hardwire
Input Circuit Breakers	63A (3 pole)
Input Phase	3-Phase
Power Factor (Input)	.99PF (100% load)
THDi	<3% (100% load)
OUTPUT	
Output Volt Amp Capacity (VA)	30000
Output kVA Capacity (kVA)	30.00
Output Watt Capacity (Watts)	27000
Output kW Capacity (kW)	27.00
Output Capacity Details	Supports up to 100% load continuously in double conversion mode; Supports 100-110% load for 10 minutes, 110 to 130% load for 1 minute and greater than 130% for 1 second before switching to bypass mode; Inverter mode is automatically restored as load levels are reduced to less than 70%; Configuration options support up to 3 S3M30KX-NIB systems wired in parallel for increased capacity or fault-tolerant, redundant operation
Power Factor	0.9
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	+/- 1%
Output Voltage Regulation (Economy Line Mode)	+/-11V of nominal



**Tripp Lite**  
 1111 W. 35th Street  
 Chicago, IL 60609 USA  
 Telephone: 773.869.1234  
 www.tripplite.com

Output Voltage Regulation (Battery Mode)	+/- 1%
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	220/380V 3-PH Wye; 230/400V 3-PH Wye; 240/415V 3-PH Wye
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Expandable Battery Runtime	Supports extended runtime with optional external battery packs
Expandable Runtime	Yes
External Battery Pack Compatibility	<p>&amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-80-9-Ah-battery~BP480V09"&gt;BP480V09&lt;/a&gt;&amp;nbsp;; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-80-10-Ah-battery~BP480V10"&gt;BP480V10&lt;/a&gt;&amp;nbsp;; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-80-10-Ah-battery~BP480V10"&gt;BP480V10&lt;/a&gt;&amp;nbsp;;-NIB; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-40-100-Ah-battery~BP480V100"&gt;BP480V100&lt;/a&gt;&amp;nbsp;; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-40-40-Ah-battery~BP480V40"&gt;BP480V40&lt;/a&gt;&amp;nbsp;; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-40-40-Ah-battery~BP480V40"&gt;BP480V40&lt;/a&gt;&amp;nbsp;;-NIB; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-40-65-Ah-battery~BP480V65"&gt;BP480V65&lt;/a&gt;&amp;nbsp;; &amp;nbsp;&lt;a class="productLink" href="//www.tripplite.com/external-ups-battery-pack-40-65-Ah-battery~BP480V65"&gt;BP480V65&lt;/a&gt;&amp;nbsp;;-NIB</p>
DC System Voltage (VDC)	+/- 240
Battery Recharge Rate (Included Batteries)	9 hours to 90% (Internal batteries)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Online, double-conversion power conditioning maintains output within 1% of the selected nominal voltage in online mode
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	LCD DISPLAY: offers a variety of graphical, text and numeric information to indicate a wide range of UPS operation and fault / warning conditions, including current operating mode, alarm status, load level, battery charge, input / output voltage & frequency, estimated runtime and more (see user manual for a detailed listing)
Switches	ON / ENTER BUTTON: turns the UPS on and confirms a selection from the settings menu; OFF / ESC BUTTON: turns off the UPS and returns to the previous item in the settings menu; TEST / UP BUTTON: initiates UPS self-test operation and advances to the next item in the settings menu; MUTE / DOWN BUTTON: silences the audible alarm and advances to the previous item in the settings menu; Press TEST/UP & MUTE/DOWN buttons simultaneously for 1 second to enter or exit the settings menu (See user manual for detailed information)
Audible Alarm	Alarms warn users of a variety of operational conditions: BYPASS MODE (beeps every 2 seconds), BATTERY MODE (beeps every 4 seconds), FAULT MODE (beeps continuously), OVERLOAD (beeps twice per second), OTHER WARNINGS (beeps once per second), FAULT (beeps continuously); All alarms can be silenced, except OVERLOAD & OTHER WARNINGS conditions
LED Indicators	4 LEDs report BYPASS / LINE / BATTERY / FAULT modes
<b>PHYSICAL</b>	
Cooling Method	Fans



**Tripp Lite**  
 1111 W. 35th Street  
 Chicago, IL 60609 USA  
 Telephone: 773.869.1234  
 www.tripplite.com

Installation Form Factors Supported with Included Accessories	Tower
Primary Form Factor	Tower
Primary UPS Depth (mm)	815
Primary UPS Height (mm)	1,000
Primary UPS Width (mm)	300
Shipping Dimensions (hwd / in.)	47.44 x 16.90 x 36.22
Shipping Weight (kg)	99.79
UPS Housing Material	Steel
UPS Power Module Dimensions (Height x Width x Depth, mm)	1000 x 300 x 815
UPS Power Module Dimensions (hwd, in.)	39.37 x 11.81 x 32.08
UPS Power Module Weight (kg)	63.50
UPS Power Module Weight (lbs.)	140
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0 to +40C (32-104F)
Storage Temperature Range	0 to +35C (32 to 95F) with battery; -15 to 60C (5 to +140F) without battery
Relative Humidity	5 to 95%, non-condensing
Operating Elevation (ft.)	< 3280ft (Capacity de-rates by 1% for every 328ft over 3280ft)
Audible Noise	<60dBA at 1meter
Operating Elevation (m)	< 1000m (Capacity de-rates by 1% for every 100m over 1000m)
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card-WEBCARDLX">WEBCARDLX</a>&nbsp;&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Programmable-RS-485-Management-Accessory-Card-for-Select-3-Phase-UPS-Systems-MODBUSCARDSV">MODBUSCARDSV</a>&nbsp;&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Programmable-Relay-I-O-Card-Tripp-Lite-SVTX-SVX-SV-UPS-Systems-RELAYCARDSV">RELAYCARDSV</a>&nbsp;&nbsp;&nbsp;&nbsp;
Network Monitoring Port Description	Card accessory slot supports network management interface or programmable I/O relay card options
Communications Cable	DB9/RS-232 cable included
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	Zero transfer time Online to Battery, Inverter to Bypass 0ms (Synchronous), and Inverter to ECO mode < 10ms.
Low Voltage Transfer to Battery Power (Setpoint)	120V(Ph-N), 208V (Ph-Ph) @ 50% load / 176V (Ph-N), 305V (Ph-Ph) @ 100% load.
High Voltage Transfer to Battery Power (Setpoint)	276 (Ph-N), 478V (Ph-Ph) @ 50% or 100% load.



<b>SPECIAL FEATURES</b>	
Grounding Lug	Yes
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Manual bypass switch; Auto Probe Monitoring (requires WEBCARDLX); Zero transfer time; On-Line/Double-Conversion
Green Energy-Saving Features	High efficiency economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	CE
Certification Details	IEC/EN 62040-1:2008+A1 (Safety); IEC/EN 62040-2:2006 (Category C3)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty
3-Phase Warranty Statement	<a href="#">Tripp Lite 3-Phase UPS Factory Warranty</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>