



Powering Business Worldwide

SCSI Double Shielded Cable (VHDCI68 to HD68 M/M), 6-ft.

MODEL NUMBER: **S444-006**



Highlights

- Premium double-shielded cable
- 34 twisted-pair conductors

System Requirements

- Any external SCSI device or controller card requiring a VHDCI68 or HD68 interface

Package Includes

- 6-ft. SCSI Cable VHDCI68M to HD68M

Description

Multi-platform SCSI III external peripheral cable VHDCI68M/HD68M. This 6ft cable is designed to connect two SCSI III (fast and wide) devices together. Manufactured using double shielded 34 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene.

Features

- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 34 twisted pair conductors
- Low-capacitance impedance matched 28 AWG stranded, tinned copper wire, insulated in polypropylene
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between

Specifications

OVERVIEW	
UPC Code	037332014221
CONNECTIONS	
Side A - Connector 1	VHDCI68 (MALE)
Side B - Connector 1	HD68 (MALE)
PHYSICAL	
Color	Black

Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.56
Shipping Weight (kg)	0.25
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.