

SmartPro 120V 3kVA 2.25kW Line-Interactive Sine Wave UPS, Extended Run, 2U Rack/Tower, NAFTA version of SMART3000RM2U

MODEL NUMBER: **SM3000RMNAFTA**



Description

3000VA line interactive UPS system for server, network and telecommunications equipment. 2U rackmount or tower form factor with an installed depth of only 19 inches. Expandable battery runtime with optional BP48V24-2U, BP48V27-2US, and BP48V60RT-3U external battery packs. Uninterruptible Power Supply (UPS) switches to battery-derived AC output during power failures and extreme voltage variations. Line interactive Automatic Voltage Regulation (AVR) offers two levels of voltage boost during brownouts and one level of voltage cut during overvoltages to maintain regulated 120v output over an input range of 83-145V. Includes L5-30P input plug and both 5-15/20R and L5-30R output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support communications via USB, DB9 serial and SNMPWEBCARD slot. HID-compliant USB port enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. Integrated 3-bank PDU switching supports load shedding and remote-reboot of connected equipment. 3-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rackmount accessories included; 2-9U STAND tower kit and 2POSTRMKITWM two post rack & wallmount accessories available. Field-replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme.

Features

- 3000VA / 2250 watt output power capacity compatible with North American 120V / 60Hz power
- 2U rack/tower UPS installs in standard 19 inch rack enclosures with an installed depth of only 19 inches
- Protects sensitive networking equipment from blackouts, voltage fluctuations and transient surges
- Line interactive Automatic Voltage Regulation (AVR) corrects inputs from 83-145VAC back to usable 120V levels without consuming battery power
- Dual boost AVR circuits boost undervoltages by 14% or 24% depending on the severity and reduces overvoltages by 12%

Highlights

- 3000VA 120V 60Hz Sine Wave 2U Expandable Rack/Tower UPS
- Dual Boost AVR Corrects Brownouts to 83V and Overvoltages to 145V
- Multiple interfaces - 1 USB, 1 DB9 and SNMPWEBCARD Slot
- Integrated Switched PDU with Current Monitoring and 3 Controllable Load Banks
- 9 Outlets (8 5-15/20R / 1 L5-30R), NEMA L5-30P input
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment

Package Includes

- SM3000RMNAFTA
- PowerAlert Software and cabling
- Mounting hardware for 4 post rackmount installation
- Warranty information
- Instruction manual



Powering Business Worldwide



- Network interfaces support simultaneous communications via USB, DB9 serial and SNMPWEBCARD slot
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, plus any number of additional servers over IP
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Communications ports support on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current monitoring, battery charge current, battery capacity, internal UPS temperature, AC line frequency, timed inverter shutoff, activate self-test and load bank output power control
- Built in Emergency Power Off (EPO) interface with cable
- Sine wave output in AC and battery modes
- Expandable runtime with optional battery packs BP48V24-2U (limit 1); BP48V27-2US (multi-pack compatible); and BP48V60RT-3U (multi-pack compatible)
- Some external battery configurations require the use of Tripp Lite's External Battery Configurator (see manual)
- Half load runtime of 9.5 minutes (1125 watts)
- Full load runtime of 3 minutes (2250 watts)
- Includes 9 output receptacles with 3 individual outlet load banks (8 NEMA 5-15/20R / 1 NEMA L5-30R)
- NEMA L5-30P input plug
- Integrated 3 bank switched PDU enables remote outlet management for load shedding or remote reboot of individual devices
- 3 stage metered LEDs offer current monitoring and battery charge level
- Mains power and voltage regulation LEDs offer at-a-glance power status information
- Front panel switches support self-test and alarm cancel functions
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user required
- Supports 2 post rackmount and wallmount installation with optional 2POSTRMKITWM accessory
- Supports upright tower placement with optional 2-9USTAND accessory
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332137821
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	L5-30P
Input Circuit Breakers	30A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 120V

OUTPUT	
Output Capacity (VA)	3000
Output Capacity (kVA)	3
Output Capacity (Watts)	2250
Output Capacity (kW)	2.2
Power Factor	0.8
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Three switchable single-outlet 5-15R load banks
Output Circuit Breakers	20A (x2) - each breaker protects 4 5-15/20R outlets, L5-30R is unbreakered
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(8) 5-15/20R; (1) L5-30R
Individually Controllable Load Banks	No
BATTERY	
Runtime Full Load (min.)	3 min. (2250w)
Runtime Half Load (min.)	9.5 min. (1125w)
Expandable Runtime	Yes
External Battery Pack Compatibility	 BP48V24-2U (limit 1); BP48V27-2US (multi-pack compatible); BP48V60RT-3U (multi-pack compatible)
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	 RBC94-2U
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 147 are reduced by 12%

Undervoltage Correction	Input voltages between 95 and 107 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 94 are boosted by 24%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Adjustable mounting rail kit included
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); Wallmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND)
Primary UPS Depth (mm)	483
Primary UPS Height (mm)	89
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	7.87 x 21.65 x 24.21
Shipping Dimensions (hwd / cm)	19.99 x 54.99 x 61.49
Shipping Weight (lbs.)	73.80
Shipping Weight (kg)	33.48
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.89 x 44.45 x 48.26
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 19
UPS Power Module Weight (kg)	29.03
UPS Power Module Weight (lbs.)	64
Unit Dimensions (hwd / in.)	3.430 x 17.320 x 19.460

ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	320
AC Mode Efficiency Rating (100% Load)	96%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	1457.1
Battery Mode Heat Dissipation (BTU/Hr) @ Half Load	472.8
COMMUNICATIONS	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; 2 USB ports, 1 DB9 serial and 1 DB9 contact closure port (4 total)
PowerAlert Software	Included
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at https://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
Communications Interface	USB (HID enabled); DB9 Serial; Contact closure
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
APPLICATIONS	
UPS Applications	High-End Desktop/Small Network
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	ENERGY STAR Qualified; FCC Part 15 Class A (USA); RoHS



Powering Business Worldwide



WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.