

## SmartPro 120V 1kVA 800W Line-Interactive Sine Wave UPS, 2U Rack/Tower, Network Card Options, LCD, USB, DB9, 6 Outlets

MODEL NUMBER: **SMART1000RM2U**



Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Ideal solution for data centers, VoIP systems and network closets.

### Features

#### Protects Mission-Critical Rack-Mounted Equipment

- Provides fully regulated sine wave AC output for servers, network storage devices and telecom hardware
- Audible alarm signals loss of utility power, overload, low battery and fault conditions
- 6 NEMA 5-15R outlets
- 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input
- 570-joule surge suppression rating

#### Reliable Battery Backup

- Supports half load up to 15 min. and full load up to 5.3 min.
- Internal batteries designed for hot-swap field replacement
- 95% line-power efficiency rating saves money in energy costs

#### Switchable Outlets

- 2 load banks, each with 2 outlets controllable remotely to reboot equipment or shed nonessential loads

#### Automatic Voltage Regulation (AVR)

- Maintains 120V nominal output over input range of 83V-147V without using battery power

### Highlights

- Corrects under- and overvoltages from 83V to 147V
- 6 NEMA 5-15R outlets—4 switchable via network interface
- Network power management and control capability
- Interactive LCD monitoring screen
- 15 min. runtime at half load; 5.3 min. at full load

### Package Includes

- SMART1000RM2U SmartPro 120V 1kVA 800W Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- EPO cable
- Mounting hardware
- Owner's manual



#### EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

#### Interactive LCD Screen

- Front-panel LCD signals operating mode, load level, voltage, battery charge and estimated runtimes
- Rotates for easy viewing in rack-mount or tower configurations

#### Network Management Cards

- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD

#### Communications Ports

- USB and DB9 ports combine with PowerAlert software, available via free download, to monitor operating conditions, monitor AC power, and enable safe unattended system shutdown and file saves in case of a prolonged power failure
- EPO port supports emergency shutdown in large facilities

#### Versatile Installation Options

- Hardware included for 4-post mounting in 2U of EIA-standard 19 in. rack
- Mounts on wall or 2-post rack with optional 2POSTRMKITWM accessory
- Mounts in upright tower position with optional 2-9USTAND accessory

## Specifications

OVERVIEW	
UPC Code	037332118806
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	15A
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase



<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	1000
Output kVA Capacity (kVA)	1.0
Output Watt Capacity (Watts)	800
Power Factor	0.8
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-21%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable two-outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(6) 5-15R
Individually Controllable Load Banks	Yes
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	5.3 min. (800w)
Half Load Runtime (min.)	15 min. (400w)
Expandable Runtime	No
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	Current version uses <a href="http://www.tripplite.com/2U-UPS-Replacement-Battery-Cartridge-for-Select-Tripp-Lite-UPS-RBC24V-LCD">RBC24V-LCD</a> ; Prior versions used <a href="http://www.tripplite.com/2U-UPS-Replacement-24VDC-Battery-Cartridge-1-set-2-select-Tripp-Lite-SmartPro-UPS-RBC92-2U">RBC92-2U</a> ; Check the label inside the battery door to verify the appropriate replacement battery part number
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 83 and 107 are boosted by 14%



<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="http://www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT">Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="http://www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ); Wallmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> )
Minimum Required Rack Depth (cm)	39.37
Minimum Required Rack Depth (inches)	15.5
Optional Mounting Accessory Notes	Optional <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ; enables upright tower UPS placement; <a href="http://www.tripplite.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ; enables wall-mount and 2-post rackmount installation; <a href="http://www.tripplite.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="http://www.tripplite.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT">Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT</a> ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	318
Primary UPS Height (mm)	88
Primary UPS Width (mm)	441
Rack Height	2U



Shipping Dimensions (hwd / cm)	22.35 x 47.24 x 58.17
Shipping Dimensions (hwd / in.)	8.80 x 18.60 x 22.90
Shipping Weight (kg)	20.77
Shipping Weight (lbs.)	45.80
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.76 x 44.07 x 31.75
UPS Power Module Dimensions (hwd, in.)	3.45 x 17.35 x 12.5
UPS Power Module Weight (kg)	16.06
UPS Power Module Weight (lbs.)	35.4
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	134
Battery Mode BTU / Hr. (Full Load)	600
AC Mode Efficiency Rating (100% Load)	95%
Audible Noise	45 dBA maximum, front side 1m
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//www.tripplite.com/SNMP-Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~SNMPWEBCARD">SNMPWEBCARD</a>&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a>&nbsp;&nbsp;&nbsp;<a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a>&nbsp;&nbsp;&nbsp;
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp+Lite">http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite</a>
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	4 milliseconds (AC to battery), 2 milliseconds (Battery to AC)
Low Voltage Transfer to Battery Power (Setpoint)	83



High Voltage Transfer to Battery Power (Setpoint)	147
<b>SPECIAL FEATURES</b>	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: <a href="http://www.tripplite.com/support/product-warranty-registration">Registration is required</a> for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="http://www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>