

## SmartPro 120V 1kVA 900W Line-Interactive Sine Wave UPS, 2U, Extended Run, Network Card Options, LCD, USB, 8 Outlets

MODEL NUMBER: **SMART1000RML2U**



Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Ideal solution for data centers, VoIP systems and network closets.

### Features

#### Protects Mission-Critical Rack-Mounted Equipment

- Provides fully regulated sine wave AC output for servers, network storage devices and telecom hardware
- Audible alarm signals loss of utility power, overload, low battery and fault conditions
- 8 NEMA 5-15R outlets
- 10-ft. (3.05 m) power cord with 120V NEMA 5-15P input
- 570-joule surge suppression rating

#### Reliable Battery Backup

- Supports half load up to 18 min. and full load up to 6.3 min.
- Internal batteries designed for hot-swap field replacement
- 97% line-power efficiency rating saves money in energy costs
- Expandable runtime with optional external battery packs, such as Tripp Lite's BP36V15-2U

#### Switchable Outlets

- 2 load banks, each with 2 outlets controllable remotely to reboot equipment or shed nonessential loads

#### Automatic Voltage Regulation (AVR)

- Maintains 120V nominal output over input range of 83V-147V without using battery power

#### EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's

### Highlights

- Corrects under- and overvoltages from 83V to 147V
- 8 NEMA 5-15R outlets—4 switchable via network interface
- Network power management and control capability
- Expandable runtime with optional external battery packs
- 18 min. runtime at half load; 6.3 min. at full load
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

### Package Includes

- SMART1000RML2U SmartPro 120V 1kVA 900W Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- EPO cable
- Mounting hardware
- Owner's manual

performance

**Interactive LCD Screen**

- Front-panel LCD signals operating mode, load level, voltage, battery charge and estimated runtimes
- Rotates for easy viewing in rack-mount or tower configurations

**Network Management Cards**

- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD

**Communications Ports**

- USB and DB9 ports combine with PowerAlert software, available via free download, to monitor operating conditions, monitor AC power, and enable safe unattended system shutdown and file saves in case of a prolonged power failure
- EPO port supports emergency shutdown in large facilities

**Versatile Installation Options**

- Hardware included for 4-post mounting in 2U of EIA-standard 19 in. rack
- Mounts on wall or 2-post rack with optional 2POSTRMKITWM accessory
- Supports front-mount installation in 4 post racks with UPSHDEARKIT accessory
- Mounts in upright tower position with optional 2-9USTAND accessory

**Specifications**

OVERVIEW	
UPC Code	037332160546
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
OUTPUT	
Output Capacity (VA)	1000
Output Capacity (kVA)	1
Output Capacity (Watts)	900



<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	570
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="//tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="//tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ); Tower ( <a href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ); Wallmount ( <a href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> );
Minimum Required Rack Depth (cm)	41.78
Minimum Required Rack Depth (inches)	16.45
Minimum Required Rack Depth with External Battery Pack (cm)	51
Minimum Required Rack Depth with External Battery Pack (in.)	20
Minimum Required Rack Depth without External Battery Pack (cm)	42
Minimum Required Rack Depth without External Battery Pack (in.)	16.5

Optional Mounting Accessory Notes	Optional <a href="//tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2-9USTAND</a> ; enables upright tower UPS placement; <a href="//tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2POSTRMKITWM</a> ; enables wall-mount and 2-post rackmount installation; <a href="//tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4POSTRAILKITWM</a> ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="//tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT">UPSHDEARKIT</a> ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary UPS Depth (mm)	342
Primary UPS Height (mm)	88
Primary UPS Width (mm)	439
Shipping Dimensions (hwd / in.)	8.60 x 23.20 x 19.20
Shipping Dimensions (hwd / cm)	21.84 x 58.93 x 48.77
Shipping Weight (lbs.)	57.40
Shipping Weight (kg)	26.04
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.76 x 43.94 x 34.16
UPS Power Module Dimensions (hwd, in.)	3.45 x 17.3 x 13.45
UPS Power Module Weight (kg)	20.64
UPS Power Module Weight (lbs.)	45.5
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	179
Battery Mode BTU / Hr. (Full Load)	542
AC Mode Efficiency Rating (100% Load)	97%
Audible Noise	45 dBA maximum, front side 1m
<b>COMMUNICATIONS</b>	
Network Management Cards	<a href="//tripplite.eaton.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a> ; <a href="//tripplite.eaton.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a>
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB, DB9 and EPO cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications

Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at <a href="https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite">https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite</a>
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	4 milliseconds (AC to battery mode), 3 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks; Schedulable daily hours of economy mode operation
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: <a href="https://tripplite.eaton.com/support/product-warranty-registration">Registration is required</a> for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="https://tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>