

SmartPro 120V 1.05kVA 650W Line-Interactive Sine Wave UPS, Tower, Network Card Options, USB, DB9, 8 Outlets

MODEL NUMBER: **SMART1050SLT**



Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Ideal solution for point-of-sale applications, VoIP systems and small business networks.

Description

The SMART1050SLT SmartPro 120V 1.05kVA 650W Line-Interactive Sine Wave UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up point-of-sale applications, VoIP systems and small business networks, the SMART1050SLT switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Featuring eight NEMA 5-15R outlets and a six-foot power cord with 120V NEMA 5-15P input, the SMART1050SLT has an internal battery that provides 19 minutes of support at half load and seven minutes at full load. Front-panel LEDs indicate line power, battery power, overload, voltage regulation and battery status. An alarm sounds to indicate power failure, low battery or overload.

Automatic voltage regulation (AVR) maintains selectable 100V, 110V or 120V nominal output over an input range of 83V to 145V without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 690-joule surge suppression rating protects your equipment from harmful power surges. With Tripp Lite's PowerAlert software (available via free download), the SMART1050SLT enables safe unattended system shutdown and file saves in case of a prolonged power failure.

Features

Protects Mission-Critical Equipment

- Provides fully regulated sine wave AC output for point-of-sale applications, VoIP systems and small

Highlights

- Corrects under- and overvoltages from 83V to 145V
- 8 NEMA 5-15R outlets
- Front-panel LEDs indicate load, power, voltage and battery statuses
- Network power management and control capability
- 19 min. runtime at half load; 7 min. at full load

Package Includes

- SMART1050SLT SmartPro 120V 1.05kVA 650W Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- Owner's manual



business networks

- Audible alarm signals loss of utility power, low battery or overload
- 8 NEMA 5-15R outlets
- 6 ft. power cord with 120V NEMA 5-15P input
- 690-joule surge suppression rating

Reliable Battery Backup

- Supports half load up to 19 min. and full load up to 7 min.
- Internal batteries designed for hot-swap field replacement
- 95% line-power efficiency rating saves money in energy costs
- Cold-start capability enables turn-on in battery mode during blackouts

Automatic Voltage Regulation (AVR)

- Maintains selectable 100V, 110V or 120V nominal output over input range of 83V–145V without using battery power

EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

LED Indicators

- Front-panel LEDs signal indicate line power, battery power, overload, voltage regulation and battery status

Network Management Cards

- Compatible with Tripp Lite UPS management card options WEBCARDLX, SNMPWEBCARD and RELAYIOCARD

Communication Ports

- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert

Telephone/Network Jacks

- Protect against power surges over telephone/DSL or network Ethernet lines

Specifications

| OVERVIEW | |
|-----------------|------------------|
| UPC Code | 037332119902 |
| UPS Type | Line-Interactive |



| INPUT | |
|--|--|
| Rated input current (Maximum Load) | 6.1A (120V), 6.6A (110V), 7.2A (100V) |
| Nominal Input Voltage(s) Supported | 100V AC; 110V AC; 120V AC |
| UPS Input Connection Type | 5-15P |
| UPS Input Cord Length (ft.) | 6 |
| UPS Input Cord Length (m) | 1.8 |
| Recommended Electrical Service | 15A 120V |
| Input Phase | Single-Phase |
| OUTPUT | |
| Output Volt Amp Capacity (VA) | 1050 |
| Output kVA Capacity (kVA) | 1.05 |
| Output Watt Capacity (Watts) | 650 |
| Nominal Voltage Details | 120V default (voltage selection via back panel switches) |
| Frequency Compatibility | 50 / 60 Hz |
| Frequency Compatibility Details | Automatic frequency selection |
| Output Voltage Regulation (Line Mode) | -13%, + 15% |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| Nominal Output Voltage(s) Supported | 100V; 110V; 120V |
| Output Receptacles | (8) 5-15R |
| Individually Controllable Load Banks | No |
| BATTERY | |
| Full Load Runtime (min.) | 7 min. (650w) |
| Half Load Runtime (min.) | 19 min. (325w) |
| DC System Voltage (VDC) | 24 |
| Battery Recharge Rate (Included Batteries) | Less than 6 hours from 10% to 90% (typical, full load discharge) |
| Internal UPS Replacement Battery Cartridge | RBC24-SLT |
| Battery Access | Battery access door |
| Battery Replacement Description | Hot-swappable, user replaceable batteries |



| | |
|---|---|
| Expandable Runtime | No |
| VOLTAGE REGULATION | |
| Voltage Regulation Description | Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 95 to 145 (120v), 87 to 133 (110v), 83 to 121 (100v) |
| Overvoltage Correction | Voltage reduction of 12% applies when input is 127 to 145 (120v), 116 to 133 (110v), 111 to 121 (100v) |
| Undervoltage Correction | Voltage boost of 14% applies when input is 95 to 108 (120v), 87 to 99 (110v), 83 to 90 (100v) |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | 2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection |
| Alarm Cancel Operation | Power-fail alarm can be silenced using alarm-cancel switch |
| Audible Alarm | Audible alarm indicates power failure and overload conditions |
| LED Indicators | Status LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level |
| Site Wiring Fault Indication | Rear panel site wiring fault LED |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 690 |
| UPS AC Suppression Response Time | Instantaneous |
| UPS Dataline Suppression | 1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet |
| EMI / RFI AC Noise Suppression | Yes |
| PHYSICAL | |
| Cooling Method | Fan |
| Installation Form Factors Supported with Included Accessories | Tower |
| Primary Form Factor | Tower |
| Primary UPS Depth (mm) | 335 |
| Primary UPS Height (mm) | 259 |
| Primary UPS Width (mm) | 173 |
| Shipping Dimensions (hwd / cm) | 33.78 x 45.47 x 23.62 |
| Shipping Dimensions (hwd / in.) | 13.30 x 17.90 x 9.30 |
| Shipping Weight (kg) | 17.42 |
| Shipping Weight (lbs.) | 38.40 |
| UPS Housing Material | Steel |
| UPS Power Module Dimensions (hwd, cm) | 25.91 x 17.27 x 33.53 |



| | |
|---|--|
| UPS Power Module Dimensions (hwd, in.) | 10.2 x 6.8 x 13.2 |
| UPS Power Module Weight (kg) | 16.33 |
| UPS Power Module Weight (lbs.) | 36 |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius. |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius. |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode BTU / Hr. (Full Load) | 107 |
| Battery Mode BTU / Hr. (Full Load) | 455 |
| AC Mode Efficiency Rating (100% Load) | 95% |
| Audible Noise | Audible Noise < 50 dBA at Front Side 1 Meter |
| COMMUNICATIONS | |
| Network Management Cards | SNMPWEBCARD WEBCARDLX RELAYIOCARD |
| Network Monitoring Port Description | Supports detailed monitoring of UPS and site power conditions |
| PowerAlert Software | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert |
| Communications Cable | USB and DB9 cabling included |
| WatchDog Compatibility | Supports Watchdog application, OS and hard-reboot restart options for remote applications. |
| Network UPS Tools Compatibility | NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite |
| Communications Interface | DB9 Serial; Slot for SNMP/Web interface; USB (HID enabled) |
| LINE / BATTERY TRANSFER | |
| Transfer Time | 4-6 milliseconds |
| Low Voltage Transfer to Battery Power (Setpoint) | 95V (120V), 87V (110V), 83V (100V) |
| High Voltage Transfer to Battery Power (Setpoint) | 145V (120V), 133V (110V), 121V (100V) |
| SPECIAL FEATURES | |
| Cold Start (Startup in Battery Mode During a Power Failure) | Cold-start operation supported |
| High Availability UPS Features | Hot swappable batteries; Auto Probe Monitoring (requires WEBCARDLX) |
| STANDARDS & COMPLIANCE | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| UPS Certifications | Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty. |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 Ultimate Lifetime Insurance |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>